


Inductive full-metal sensor

IFB2004BARKG/AM/SC/0,3M/US/2LE



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	4
Housing	threaded type
Dimensions [mm]	M12 x 1 / L = 40

Application

Special feature	Gold-plated contacts; Increased sensing range; Full-metal housing; Optical setting aid; anti-spatter
Application	Use in welding applications

Electrical data

Operating voltage [V]	10...36 DC
Protection class	III
Reverse polarity protection	yes



Inductive full-metal sensor

IFB2004BARKG/AM/SC/0,3M/US/2LE

Outputs		
Electrical design		PNP/NPN
Output function		normally open
Max. voltage drop switching output DC [V]		2.5
Minimum load current [mA]		2
Max. leakage current [mA]		0.6
Permanent current rating of switching output DC [mA]		100
Switching frequency DC [Hz]		75
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Detection zone		
Sensing range [mm]		4
Operating distance [mm]		0...3.25
Increased sensing range		yes
Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.2 / aluminium: 0.1 / copper: 0	
Hysteresis [% of Sr]	1...20	
Operating conditions		
Ambient temperature [°C]	-25...70	
Protection	IP 67	
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011 emission	class B
Impact resistance		1 J
MTTF [years]	1422	
UL approval	Ta	0...40 °C
	Enclosure type	Type 1
	voltage supply	Limited Voltage/Current
	File number UL	E174191
Mechanical data		
Weight [g]	49	
Housing	threaded type	
Mounting	flush mountable	
Dimensions [mm]	M12 x 1 / L = 40	
Thread designation	M12 x 1	
Materials	housing: stainless steel (1.4404 / 316L) anti-spatter; sensing face: stainless steel (1.4404 / 316L) anti-spatter; cable plug: PA; lock nuts: stainless steel (1.4404 / 316L) anti-spatter	
Full-metal housing	yes	

IFR203



Inductive full-metal sensor

IFB2004BARKG/AM/SC/0,3M/US/2LE

Displays / operating elements

Display	switching status	1 x LED, green
	setting aid	1 x LED, red
Optical setting aid	yes	

Accessories

Accessories (supplied)	lock nuts: 2
------------------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------


Electrical connection - plug

Cable: 0.3 m, PVC; 2 x 0.5 mm²

Connector: 1 x M12; Contacts: gold-plated



Connection



IFR203



Inductive full-metal sensor

IFB2004BARKG/AM/SC/0,3M/US/2LE

Diagrams and graphs

Installation

