

Pneumatic turbine grinder GT 652 D

Oil-free operation

**MANNESMANN
DEMAG**

Advantage

- High degree of concentricity for long run-times

Delivery

Includes hose unit and collet chuck keys



Art. no.	75061 025
Brand	MANNESMANN DEMAG
Manufacturer Part Number	29940375
Model	GT 652 D
Valve design	Rotary valve
Max. idle speed	65000 rpm
Power output	70 W
Air consumption	3.5 l/s
Sound-pressure level	66 dB
Length	173 mm
Diameter of housing	17 mm
Max. clamping diameter	3 mm
Collet chuck diameter	3 mm
Suitable for max. sanding block diameter	6 mm
Max. HM rotating milling cutter diameter	4 mm
Weight	0.27 kg
Gross Weight	0.400 kg
Product Group	7AA

EAN

4251757302787