


7.62mm standard profile vertical rising clamp terminal blocks

Product overview


- 2 and 3 pole double interlocking mechanism for increased strength
- 4-12 pole pre-assembled
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- Cable acceptance - 0.2-2.0mm² (30-12AWG)
- Guided pin alignment
-  approved

CTBP0118



SPECIFICATION	
Rating	UL=20A/300V, VDE=24A/450V
Impulse withstand voltage	1600V/1min
Working temperature	-40°C to +105°C
Moulding	UL94-V0 flame retardant PA66
Pin/terminal	Tinned, nickel plated brass
Rising clamp	Tinned, nickel plated brass
Screw/torque	M3 steel zinc plated, 0.5Nm
Recommended PCB hole size	ø1.6mm

PART NO.	POLES	LENGTH
CTBP0118/2	2	15.24mm
CTBP0118/3	3	22.86mm
CTBP0118/4	4	30.48mm
CTBP0118/5	5	38.10mm
CTBP0118/6	6	45.72mm
CTBP0118/7	7	53.34mm
CTBP0118/8	8	60.96mm
CTBP0118/9	9	68.58mm
CTBP0118/10	10	76.20mm
CTBP0118/11	11	83.82mm
CTBP0118/12	12	91.44mm



KEY FEATURES

Standard profile | Double interlock mechanism | Professional rising clamp

