


AW-HE145W [White Model]
AW-HE145K [Black Model]
HD Integrated Camera For Indoor Use

US and Europe Only Model



# Various features that meet high shooting demands

## High-Quality Full-HD60p/50p Shooting

Full-HD output and 59.94p/50p shooting achieve extremely smooth video, even in live sports and other environments containing rapid movement.

## **Multiple Interfaces Supported**

A wide range of outputs are supported: 3G-SDI, HDMI and IP.

#### • Rear View



## SRT<sup>1</sup> support for stable video transmission over public lines



SRT, a next-generation video transmission protocol with strong security suitable for unstable network environments, is supported.

1: SRT: Secure Reliable Transport.

## **Useful Software for Simplifies Workflow**

Compatible with a wide range of software, including the Auto Tracking Software Key and PTZ Control Center. This software will simplify the workflow of the PTZ camera shooting and reduces the burden of operation and management.

#### Other Features

- · HDR (HLG) Support
- Night Mode Support
- Adaptive Matrix prevents color overloaded from blue LEDs
- Optical Image Stabilizer (OIS) Loaded
- Equipped with a Large Tally Lamp
- JPEG Image Saving Function Equipped
- NDI | HX Compatibility for Excellent Video Streaming Quality<sup>1</sup>
- Direct Broadcast via RTMP (Real-Time Messaging Protocol)
- AW-RP150GJ Connection for Large-Scale Production Systems
- Controlled by Web UI

1: Need to activate

## **Accessories**



#### Remote Camera Controller **AW-RP150**

High operability ensured through touch-panel GUI monitor and a new type of joystick.



Remote Camera Controller AW-RP60

Equipped with a GUI menu screen for clear visibility and a joystick for intuitive control.



Auto Tracking Software Key AW-SF100/AW-SF200

Face Recognition and Human Body Detection for High Precision and Smooth Tracking Control for Natural-looking Video.



Visual Preset Software Key **AW-SF300** 

GUI screen that enables the subject of multiple PTZ Cameras to be switched with a single click of an icon

# **Panasonic**®

Panasonic Connect Co., Ltd. 2-15 Matsuba-cho, Kadoma, Osaka 571-8503 Japan

SP-HE145PE2WEB 202204U




Factories of Panasonic Connect Co., Ltd. have received ISO14001: 2015-the Environmental Management System certification. (Except for 3rd party's peripherals.)

### AW-HE145W/K Specifications<sup>1</sup>

General		
Power Requirements		12 V DC (10.8 V to 13.2 V)
PoE++		IEEE802.3bt: DC 42 V to 57 V
Current Consumption		4.0 A (XLR IN connector), 1.2 A (PoE++ power supply)
Weight		Approx. 4.1 kg (9.04 lb) (excluding mount bracket)
Dimensions (W x H x D)		213 mm x 267 mm x 219 mm (8-3/8 inches x 10-1/2 inches x 8-5/8 inches) (excluding protrusions, direct ceiling mount bracket)
Camera Unit Effective Pixels		20.18 million pixels
		·
Imaging Sensors		1-type Full-HD MOSx1
Lens		Motorized Optical 20x zoom, F2.8 to F4.5 [=8.8 mm [11/32 inches] to 176.0 mm [6-15/16 inches]; 35 mm [1-3/8 inches] equivalent: 24.5 mm [31/32 inches] to 490.0 mm [19-9/32 inches]]
Zoom		Optical zoom: 20x     i.Zoom: FHD 32x     Digital zoom: 10x
Angle of View Range		Horizontal angle of view: 75.1° (wide) to 4.0° (tele) Vertical angle of view: 46.7° (wide) to 2.3° (tele) Diagonal angle of view: 82.8° (wide) to 4.6° (tele)
Horizontal Resolution		1,000 TV lines Typ (Center area)
Output Format		1880/59,94p, 1080/50p, 1080/29,97p², 1080/29,97PsF, 1080/25p², 1080/25PsF, 1080/23,98p 1080/24p², 1080/23,98p², 1080/23,98PsF, 1080/59,94i, 1080/50i, 720/59,94p, 720/50p
Output		
HDMI		HDMI 2.0 standard, 4:2:2/10bit
3G-SDI OUT		SMPTE292M, 424M / 75 Ω (BNC x 1)
Input/Output		
LAN		LAN connector for IP control (RJ-45)
RS-422		CONTROL IN RS-422A (RJ-45)
MIC/LINE input		AAC compatible (compatible with IP only), ø 3.5 mm stereo mini jack, Input impedance: Approx. 10 kΩ (unbalanced)
During MIC input		Supported mic: Stereo mic (plug-in power, on/off switching via menu) Supply voltage: 2.5 V ± 0.5 V Mic input sensitivity: Approx. –40 dBV (0 dB=1 V/Pa, 1 kHz)
During LINE input		Input level: Approx. –10 dBV
Pan-tilt Head Unit	2 mpat	input teret. Approx. To apr
Panning Range		±175°
Tilting range		-30° to 210°4
IP Streaming		-30 (0.210 -
Image Streaming Mode		IDEO (MIDEO) ILOVA ILOVE
		JPEG (MJPEG), H.264, H.265
Image Resolution		1920x1080, 1280x720, 640x360, 320x180
Image Transmission Setti		III : A ALITO
NDIIHX	Transmission Type	Unicast port (AUTO) Unicast port (MANUAL) Multicast port
	Frame Rate	[60Hz] 60fps / 30fps / 15fps / 5fps [50Hz] 50fps / 25fps / 12.5fps / 5fps
	Max Bit Rate	24576kbps / 20480kbps / 16384kbps / 14336kbps / 12288kbps / 10240kbps / 8192kbps / 6144kbps / 4096kbp / 3072kbpss / 2048kbps / 1536kbps / 1024kbps / 768kbps / 512kbps Unicast port (AUTO)
	Туре	Unicast port (MANUAL) Multicast port
	Frame Rate	[60Hz] 60fps / 30fps / 15fps / 5fps [50Hz] 50fps / 25fps / 12.5fps / 5fps
	Max Bit Rate	24576kbps / 20480kbps / 16384kbps / 14336kbps / 12288kbps / 10240kbps / 8192kbps / 6144kbps / 4096kbp / 3072kbpss / 2048kbps / 1536kbps / 1024kbps / 768kbps / 512kbps
SRT H.265	Transmission Type	Unicast port (AUTO) Unicast port (MANUAL) Multicast port
	Frame Rate	[60Hz] 60fps / 30fps [50Hz] 50fps / 25fps
	Max Bit Rate	24576kbps / 20480kbps / 16384kbps / 14336kbps / 12288kbps / 10240kbps / 8192kbps / 6144kbps / 4096kbp / 3072kbpss / 2048kbps / 1536kbps / 1024kbps / 768kbps / 512kbps

Product specifications are subject to change without notice.







Professional

**AV Website** 

Broadcast and Contact Information







Mobile App

<sup>•</sup> NDI® is a new protocol developed by NewTek, Inc. that supports IP video production workflow. NDI® is a registered trademark of NewTek, Inc. in the United States and other countries. In this instance, NDI® IHX is used to indicate high efficiency low bandwidth NDI® IHX.