


7111 | 7111HV

The 7111 series counter is feature packed with an unrivalled performance ratio, suitable for thousands of applications




Key Features

- Use of the latest CMOS circuitry achieves an expected battery life of 10 years.
- Connection using built in screw terminals (on all models).
- 9mm black high contrast LCD display.
- Backlight (externally powered) 5VDC.
- Counting up to 10kHz. (7111)
- 7111HV permits triggering from any voltage between 10-240VAC or 10VDC-110VDC ±10%.
- Contact closure/open collector low speed count input with integral de-bounce circuitry (7111 model).
- Choice of mounting available, front panel with supplied bezel or rear mounting clip.
- Front panel can be sealed to IP65.
- Installation is simplified all models have screw connections on rear for quick and simple connection.
- CE, UL and cUL approved.

Applications


- Replacement for electro-mechanical counters
- Applications where external power is not readily available.
- Position, length, rotation and distance measuring applications.
- Event counting
- Water meters remote display





Water Meter Wiring

Our most popular remote display for water meters is the 7111 counter. It is easy to install with a two wire hookup.



Specifications 7111

Direction Input	Connection or electronic input TTL/CMOS compatible. Add=no connection or >2.4v (logic 1); Subtract=connect to COMMON or <0.7v (logic 0). Direction input must precede count input by 5µS (minimum) for valid operation.
External Reset	Contact closure/open collector, negative edge triggered, 0.7v threshold, 15mS minimum closure time.
Low Speed Count Input	Contact closure/open collector with integral de-bounce circuitry. 30Hz maximum, negative edge triggered, 0.7v threshold, 15mS minimum closure time. Max 18VDC.
High Speed Count Input	Electronic input 10kHz maximum, negative edge triggered, 0.7v threshold 50µS minimum pulse length, TTL/ CMOS Compatible. Max 18VDC.

Specifications 7111HV

External Reset	10-110VDC ±10%, 10-240VAC ±10%, 50mS minimum length.
Direction Input	Connection or electronic input TTL/CMOS compatible. Add=no connection or >2.4v (logic 1); Subtract=connect to COMMON or <0.7v (logic 0). Direction input must precede count input by 5µS (minimum) for valid operation. Max 18VDC.
Count Input	10-110VDC± 10%, 10-240VAC± 10%, 50mS minimum pulse width, 10Hz.

Part Numbers:

7111 7111HV Totalising counter Counter with HV inputs



www.trumeter.com

Frumeter (Europe) Pilot Mill

Alfred Street Bury, BL9 9EF Tel: +44 161 674 0960 Email: sales.uk@trumeter.com

Trumeter (The Americas) 702 S. Military Trail

Deerfield Beach, Florida FL 33442, USA Tel: +1 954 725 6699 Email: sales.usa@trumeter.com

Innovative Design Technologies Sdn. Bhd Lot 5881, Lorong Iks Bukit Minyak 1 Taman Perindustrian Iks, 14000 Bukit Tengah Penang, Malaysia Web: www.idtworld.com Tel: + 604 5015700 Tel: + 604 5015700 Email: sales.my@idtworld.com