

GENTECH INTERNATIONAL LTD

LIQUID LEVEL SENSORS

LS Series - Horizontal Level Sensor

Grangestone Industrial Estate Girvan, Ayrshire KA26 9PS United Kingdom

Telephone: +44 1465 713581 Fax: +44 1465 714974

E-Mail: info@gentechsensors.com Web Site www.gentechsensors.com

LS803-51

Design Features

- High or low level sensing
- External & Internal fitting options
- Reed Switch reliability
- Silicone sealing components
- Easy installation



Product Comments

- UL listed model, File E98428
- Normally open or normally closed by rotating through 180°
- Suitable for a wide range of liquids
- Interface option available
- Polypropylene Materials

Typical Applications

- Drinking water level
- Coolant level indication
- Cooling systems
- Water high or low Level
- Waste Water Level


| Material, Design and Operation | |
|---------------------------------|---------------------------------------|
| | |
| Mounting: | Side Entry |
| Material: | Polypropylene |
| _ Fitting | External & Internal Universal Fitting |
| Contact Form: | Form A - SPST |
| Contact Material: | Ruthenium |
| Maximum Switching Volts: | 250 VAC |
| Maximum Switching Current: | 1.0 |
| Maximum Power: | 15 Watts |
| Housing Temperature Range °C: | 80 |
| Housing Material: | Glass Filled Polypropylene |
| Housing Colour: | Charcoal |
| Float Material: | Glass Filled Polypropylene |
| Connection Type: | Stripped Cables |
| Cable Type: | 2 x 18AWG 32/0.2mm PVC insulated |
| | 0.5m long to UL/CSA/BS6361 |
| Cable Colour: | Black/Black |
| Minimum Specific Gravity: | 0.65 |
| Operating Temperature Range °C: | 80 |
| Operating Pressure BAR: | 4 |
| Sealing Components: | Silicone |
| Mounting Shock: | 50g for 11ms duration |
| Mounting Vibration: | 35g up to 500Hz |
| Operate Mode: | N/C with float Horizontal |







Line Drawing


Internal Fitting








External Fitting





EXTERNAL FITTING

