

Height-adjustable material stands - in increments

Application:

For providing materials in plastic and sheet steel boxes, wire baskets etc. directly at workstations.

Execution:

- Profile steel/tube construction with sheet steel platform
- Sheet steel platform with all-round edge 20 mm high
- Platform does not tilt
- Height-adjustable in increments of 25 mm

Delivery:

Disassembled



| | |
|------------------------------------|-----------------------|
| Art. no. | 50261 013 |
| Brand | FETRA |
| Manufacturer Part Number | 1890 |
| Material of loading surface | Steel plate |
| Suitable for transporting | Electrical components |
| Load-carrying capacity | 150 kg |
| Number of loading surfaces | 1 |
| Loading surface size | 605 x 405 mm |
| ESD-capable | Yes |
| Number of fixed rollers | 0 |
| Number of steering rollers | 4 PCS |
| With wheel lock | Yes |
| Total stop optional | No |
| Wheel width | 25 mm |
| Wheel diameter | 75 mm |
| Material of wheel | TPE-ESD |
| Colour | Slate grey RAL 7015 |
| Surface | Powder-coated |
| Gross Weight | 15.000 kg |
| Product Group | 5AB |

EAN

4017976171890