

Revisione n. 1

Data revisione 29/01/2016

Stampata il 10/10/2017

Pagina n. 1/12

Safety data sheet

SECTION 1. Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Code

Product name

Rein ST-605 BROWN Solid compound Rein ST-605

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.3. Details of the supplier of the safety data sheet

SAINT-GOBAIN ABRASIVES Conflance Sainte Honorine FRANCE



Chris.quinn@saint-gobain.com

For the data sheet

1.4. Emergency telephone number

For urgent inquiries refer to Orfila +33 01 45 42 59 59

SECTION 2. Hazards identification.

2.1. Classification of the substance or mixture.

The product is classified as hazardous pursuant to the provisions set forth in EC Regulation 1272/2008 (CLP) (and subsequent amendments and supplements). The product thus requires a safety datasheet that complies with the provisions of EC Regulation 1907/2006 and subsequent amendments. Any additional information concerning the risks for health and/or the environment are given in sections 11 and 12 of this sheet.

Hazard classification and indication: Eye irritation, category 2 Skin irritation, category 2

H319 H315 Causes serious eye irritation. Causes skin irritation.

2.2. Label elements.

Hazard labelling pursuant to EC Regulation 1272/2008 (CLP) and subsequent amendments and supplements.



Warning



Revisione n. 1

Data revisione 29/01/2016

Stampata il 10/10/2017

Pagina n. 2/12

Hazard statements:

H319	Causes serious eye irritation.
H315	Causes skin irritation.

Precautionary statements:

P264	Accurately wash thoroughly after handling.
P280	Wear protective gloves / eye protection / face protection.
P302+P352	IF ON SKIN: wash with plenty of water.
P332+P313	If skin irritation occurs: Get medical advice / attention.

2.3. Other hazards.

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

SECTION 3. Composition/information on ingredients.

3.1. Substances.

Information not relevant.

3.2. Mixtures.

Contains:

Identification.	Conc. %.	Classification 1272/2008 (CLP).
STEARIC ACID		(0).
CAS. 57-11-4	10 - 15	Eye Irrit. 2 H319, Skin Irrit. 2
EC. 200-313-4		H315, STOT SE 3 H335
INDEX		
CROMIUM OXIDE (III) (68,42% - metallic elemen	nt)	
CAS. 1308-38-9	0 - 1	
EC. 215-160-9		
INDEX		

Note: Upper limit is not included into the range.

The full wording of hazard (H) phrases is given in section 16 of the sheet.

SECTION 4. First aid measures.

4.1. Description of first aid measures.

EYES: Remove contact lenses, if present. Wash immediately with plenty of water for at least 15 minutes, opening the eyelids fully. If problem persists, seek medical advice. SKIN: Remove contaminated clothing. Wash immediately with plenty of water. If irritation persists, get medical advice/attention. Wash contaminated



Revisione n. 1

Data revisione 29/01/2016

Stampata il 10/10/2017

Pagina n. 3/12

clothing before using it again.

INHALATION: Remove to open air. In the event of breathing difficulties, get medical advice/attention immediately. INGESTION: Get medical advice/attention. Induce vomiting only if indicated by the doctor. Never give anything by mouth to an unconscious person, unless authorised by a doctor.

4.2. Most important symptoms and effects, both acute and delayed.

For symptoms and effects caused by the contained substances, see chap. 11.

4.3. Indication of any immediate medical attention and special treatment needed.

Information not available.

SECTION 5. Firefighting measures.

5.1. Extinguishing media.

SUITABLE EXTINGUISHING EQUIPMENT The extinguishing equipment should be of the conventional kind: carbon dioxide, foam, powder and water spray. UNSUITABLE EXTINGUISHING EQUIPMENT None in particular.

5.2. Special hazards arising from the substance or mixture.

HAZARDS CAUSED BY EXPOSURE IN THE EVENT OF FIRE Do not breathe combustion products.

5.3. Advice for firefighters.

GENERAL INFORMATION

Use jets of water to cool the containers to prevent product decomposition and the development of substances potentially hazardous for health. Always wear full fire prevention gear. Collect extinguishing water to prevent it from draining into the sewer system. Dispose of contaminated water used for extinction and the remains of the fire according to applicable regulations.

SPECIAL PROTECTIVE EQUIPMENT FOR FIRE-FIGHTERS

Normal fire fighting clothing i.e. fire kit (BS EN 469), gloves (BS EN 659) and boots (HO specification A29 and A30) in combination with self-contained open circuit positive pressure compressed air breathing apparatus (BS EN 137).

SECTION 6. Accidental release measures.

6.1. Personal precautions, protective equipment and emergency procedures.

Block the leakage if there is no hazard.

Wear suitable protective equipment (including personal protective equipment referred to under Section 8 of the safety data sheet) to prevent any contamination of skin, eyes and personal clothing. These indications apply for both processing staff and those involved in emergency procedures.



Data revisione 29/01/2016





SAFETY DATA SHEET FOR SOLID COMPOUND

Pagina n. 4/12

6.2. Environmental precautions.

The product must not penetrate into the sewer system or come into contact with surface water or ground water.

6.3. Methods and material for containment and cleaning up.

Collect the leaked product into a suitable container. Evaluate the compatibility of the container to be used, by checking section 10. Absorb the remainder with inert absorbent material.

Make sure the leakage site is well aired. Check incompatibility for container material in section 7. Contaminated material should be disposed of in compliance with the provisions set forth in point 13.

6.4. Reference to other sections.

Any information on personal protection and disposal is given in sections 8 and 13.

SECTION 7. Handling and storage.

7.1. Precautions for safe handling.

Before handling the product, consult all the other sections of this material safety data sheet. Avoid leakage of the product into the environment. Do not eat, drink or smoke during use. Remove any contaminated clothes and personal protective equipment before entering places in which people eat.

7.2. Conditions for safe storage, including any incompatibilities.

Store only in the original container. Store the containers sealed, in a well ventilated place, away from direct sunlight. Keep containers away from any incompatible materials, see section 10 for details.

7.3. Specific end use(s).

Information not available.

SECTION 8. Exposure controls/personal protection.

8.1. Control parameters.

Regulatory References:

CZE	Česká Republika	Nařízení vlády č. 361/2007 Sb. kterým se stanoví podmínky ochrany zdraví při práci
DEU	Deutschland	MAK-und BAT-Werte-Liste 2012
FRA	France	JORF n°0109 du 10 mai 2012 page 8773 texte n° 102
GRB	United Kingdom	EH40/2005 Workplace exposure limits

Revisione n. 1 Data revisione 29/01/2016 Stampata il 10/10/2017 SAFETY DATA SHEET SAINT-GOBAIN FOR SOLID COMPOUND Pagina n. 5/12 GRC Ελλάδα ΕΦΗΜΕΡΙΣ ΤΗΣ ΚΥΒΕΡΝΗΣΕΩΣ -ΤΕΥΧΟΣ ΠΡΩΤΟ Αρ. Φύλλου 19 - 9 Φεβρουαρίου 2012 HUN Magyarország 50/2011. (XII. 22.) NGM rendelet a munkahelyek kémiai biztonságáról ITA Italia Decreto Legislativo 9 Aprile 2008, n.81 POL Polska ROZPORZĂDZENIE MINISTRA PRACY I POLITYKI SPOŁECZNEJ z dnia 16 grudnia 2011r ΕU OEL EU Directive 2009/161/EU; Directive 2006/15/EC; Directive 2004/37/EC; Directive 2000/39/EC. **TLV-ACGIH** ACGIH 2014

ALUMINUM OXIDE Threshold Limit Value.							
Туре	Country	TWA/8h		STEL/15min			
		mg/m3	ppm	mg/m3	ppm		
TLV	CZE	0,1					
MAK	DEU	1,5					
MAK	DEU	4				INHAL.	
MAK	DEU	0,3				RESP.	
VLEP	FRA	10					
WEL	GRB	4					
TLV	GRC		10				
AK	HUN	6					
NDS	POL	1,2				RESP.	
NDS	POL	2,5				INHAL.	
TLV-ACGIH		1	0,9				
STEARIC ACID							
Threshold Limit Value.	Country	TWA/8h		STEL/15min			
	·	mg/m3	ppm	mg/m3	ppm		
TLV-ACGIH		0,1		0,2			
CROMIUM OXIDE (III)							
Threshold Limit Value.	Country	TWA/8h		STEL/15min			
Type	Country	mg/m3	ppm	mg/m3	ppm		
TLV	ITA	0,5	ppin	ilig/ilio	PP'''		
OEL	EU	2					
TLV-ACGIH	LU						
I LV-AUGIH		0,5					

Legend:

(C) = CEILING ; INHAL = Inhalable Fraction ; RESP = Respirable Fraction ; THORA = Thoracic Fraction.

8.2. Exposure controls.

As the use of adequate technical equipment must always take priority over personal protective equipment, make sure that the workplace is well aired through effective local aspiration. Personal protective equipment must be CE marked, showing that it complies with applicable standards.

Data revisione 29/01/2016

Stampata il 10/10/2017

SAFETY DATA SHEET FOR SOLID COMPOUND

Pagina n. 6/12

Provide an emergency shower with face and eye wash station.

HAND PROTECTION

ՠՈՌ

SAINT-GOBAIN

Protect hands with category III work gloves (see standard EN 374).

The following should be considered when choosing work glove material: compatibility, degradation, failure time and permeability. The work gloves' resistance to chemical agents should be checked before use, as it can be unpredictable. The gloves' wear time depends on the duration and type of use.

SKIN PROTECTION

Wear category II professional long-sleeved overalls and safety footwear (see Directive 89/686/EEC and standard EN ISO 20344). Wash body with soap and water after removing protective clothing.

EYE PROTECTION

Wear airtight protective goggles (see standard EN 166).

RESPIRATORY PROTECTION

If the threshold value (e.g. TLV-TWA) is exceeded for the substance or one of the substances present in the product, use a mask with a type B filter whose class (1, 2 or 3) must be chosen according to the limit of use concentration. (see standard EN 14387). In the presence of gases or vapours of various kinds and/or gases or vapours containing particulate (aerosol sprays, fumes, mists, etc.) combined filters are required.

Respiratory protection devices must be used if the technical measures adopted are not suitable for restricting the worker's exposure to the threshold values considered. The protection provided by masks is in any case limited.

If the substance considered is odourless or its olfactory threshold is higher than the corresponding TLV-TWA and in the case of an emergency, wear opencircuit compressed air breathing apparatus (in compliance with standard EN 137) or external air-intake breathing apparatus (in compliance with standard EN 138). For a correct choice of respiratory protection device, see standard EN 529.

ENVIRONMENTAL EXPOSURE CONTROLS.

The emissions generated by manufacturing processes, including those generated by ventilation equipment, should be checked to ensure compliance with environmental standards.

SECTION 9. Physical and chemical properties.

9.1. Information on basic physical and chemical properties.

SAINT-GOBAIN	SAFET FOR SC
Oxidising properties	Not available.

Data revisione 29/01/2016

Stampata il 10/10/2017

Y DATA SHEET LID COMPOUND

Pagina n. 7/12

9.2. Other information.

Solid content. VOC (Directive 2010/75/EC) : VOC (volatile carbon) :

100,00 %

0

0

SECTION 10. Stability and reactivity.

10.1. Reactivity.

There are no particular risks of reaction with other substances in normal conditions of use.

10.2. Chemical stability.

The product is stable in normal conditions of use and storage.

10.3. Possibility of hazardous reactions.

No hazardous reactions are foreseeable in normal conditions of use and storage.

10.4. Conditions to avoid.

None in particular. However the usual precautions used for chemical products should be respected.

10.5. Incompatible materials.

Information not available.

10.6. Hazardous decomposition products.

Information not available.

SECTION 11. Toxicological information.

11.1. Information on toxicological effects.

In the absence of experimental data for the product itself, health hazards are evaluated according to the properties of the substances it contains, using the criteria specified in the applicable regulation for classification. It is therefore necessary to take into account the concentration of the individual hazardous substances indicated in section 3, to evaluate the toxicological effects of exposure to the product.

Data revisione 29/01/2016 Stampata il 10/10/2017



SAFETY DATA SHEET FOR SOLID COMPOUND

Pagina n. 8/12

Acute effects: stinging eyes. Symptoms may include: rubescence, edema, pain and lachrymation. Ingestion may cause health problems, including stomach pain and sting, nausea and sickness.

Acute effects: contact with skin may cause: irritation, erythema, edema, dryness and chapped skin. Ingestion may cause health disorders, including stomach pain and sting, nausea and sickness.

SECTION 12. Ecological information.

Use this product according to good working practices. Avoid littering. Inform the competent authorities, should the product reach waterways or contaminate soil or vegetation.

12.1. Toxicity. Information not available.

12.2. Persistence and degradability.

STEARIC ACID	
Solubility in water.	< 50 mg/l
Rapidly biodegradable.	

CROMIUM OXIDE (III)	
Solubility in water.	< 0,001 mg/l
Biodegradability: Information not available.	

12.3. Bioaccumulative potential.

STEARIC ACID	
Partition coefficient: n- octanol/water.	> 5
BCF.	234

12.4. Mobility in soil.

Information not available.

12.5. Results of PBT and vPvB assessment.

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

12.6. Other adverse effects.

Information not available.

SECTION 13. Disposal considerations.



Data revisione 29/01/2016





SAFETY DATA SHEET FOR SOLID COMPOUND

Pagina n. 9/12

13.1. Waste treatment methods.

Reuse, when possible. Product residues should be considered special hazardous waste. The hazard level of waste containing this product should be evaluated according to applicable regulations.

Disposal must be performed through an authorised waste management firm, in compliance with national and local regulations. CONTAMINATED PACKAGING

Contaminated packaging must be recovered or disposed of in compliance with national waste management regulations.

SECTION 14. Transport information.

14.1. UN number.

Not applicable.

14.2. UN proper shipping name.

Not applicable.

14.3. Transport hazard class(es).

Not applicable.

14.4. Packing group.

Not applicable.

14.5. Environmental hazards.

Not applicable.

14.6. Special precautions for user.

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code.

		Revisione n. 1
		Data revisione 29/01/2016
		Stampata il 10/10/2017
	SAFETY DATA SHEET	
SAINT-GOBAIN	FOR SOLID COMPOUND	
		Pagina n. 10/12
Information not relevant.		
SECTION 15. Regulatory	information.	
Ū į		
15.1. Safety, health and environme	ental regulations/legislation specific for the substance or mixture.	
	Nana	
Seveso category.	None.	
Restrictions relating to the product or o	contained substances pursuant to Annex XVII to EC Regulation 1907/2006	<u>.</u>
		_
Product. Point.	3	
F OIN.	5	
Substances in Candidate List (Art. 59	REACH)	
Substances in Candidate List (Art. 59		
None.		
Substances subject to authorisarion (A	Innex XIV REACH).	
None.		
Substances subject to exportation repo	orting pursuant to (EC) Reg. 689/2008:	
None.		
Substances subject to the Rotterdam (Convention:	
None.		
Substances subject to the Stockholm (Convention	
None.		
Healthcare controls.		
Workers exposed to this chemical agent must not undergo health checks, provided that available risk-assessment data prove that the risks related to the		
workers' health and safety are modest and that the 98/24/EC directive is respected.		
15.2. Chemical safety assessment		

No chemical safety assessment has been processed for the mixture and the substances it contains.

SECTION 16. Other information.

Text of hazard (H) indications mentioned in section 2-3 of the sheet:

Eye Irrit. 2

Eye irritation, category 2



Revisione n. 1

Data revisione 29/01/2016

Stampata il 10/10/2017

Pagina n. 11/12

Skin Irrit. 2Skin irritation, category 2STOT SE 3Specific target organ toxicity - single exposure, category 3H319Causes serious eye irritation.H315Causes skin irritation.H335May cause respiratory irritation.

LEGEND:

- ADR: European Agreement concerning the carriage of Dangerous goods by Road
- CAS NUMBER: Chemical Abstract Service Number
- CE50: Effective concentration (required to induce a 50% effect)
- CE NUMBER: Identifier in ESIS (European archive of existing substances)
- CLP: EC Regulation 1272/2008
- DNEL: Derived No Effect Level
- EmS: Emergency Schedule
- GHS: Globally Harmonized System of classification and labeling of chemicals
- IATA DGR: International Air Transport Association Dangerous Goods Regulation
- IC50: Immobilization Concentration 50%
- IMDG: International Maritime Code for dangerous goods
- IMO: International Maritime Organization
- INDEX NUMBER: Identifier in Annex VI of CLP
- LC50: Lethal Concentration 50%
- LD50: Lethal dose 50%
- OEL: Occupational Exposure Level
- PBT: Persistent bioaccumulative and toxic as REACH Regulation
- PEC: Predicted environmental Concentration
- PEL: Predicted exposure level
- PNEC: Predicted no effect concentration
- REACH: EC Regulation 1907/2006
- RID: Regulation concerning the international transport of dangerous goods by train
- TLV: Threshold Limit Value
- TLV CEILING: Concentration that should not be exceeded during any time of occupational exposure.
- TWA STEL: Short-term exposure limit
- TWA: Time-weighted average exposure limit
- VOC: Volatile organic Compounds
- vPvB: Very Persistent and very Bioaccumulative as for REACH Regulation
- WGK: Water hazard classes (German).

GENERAL BIBLIOGRAPHY

- 1. Regulation (EU) 1907/2006 (REACH) of the European Parliament
- 2. Regulation (EU) 1272/2008 (CLP) of the European Parliament
- 3. Regulation (EU) 790/2009 (I Atp. CLP) of the European Parliament
- 4. Regulation (EU) 2015/830 of the European Parliament
- 5. Regulation (EU) 286/2011 (II Atp. CLP) of the European Parliament
- 6. Regulation (EU) 618/2012 (III Atp. CLP) of the European Parliament
- 7. Regulation (EU) 487/2013 (IV Atp. CLP) of the European Parliament
- 8. Regulation (EU) 944/2013 (V Atp. CLP) of the European Parliament
- 9. Regulation (EU) 605/2014 (VI Atp. CLP) of the European Parliament
- The Merck Index. 10th Edition
- Handling Chemical Safety
- INRS Fiche Toxicologique (toxicological sheet)
- Patty Industrial Hygiene and Toxicology
- N.I. Sax Dangerous properties of Industrial Materials-7, 1989 Edition
- ECHA website
- Note for users:

The information contained in the present sheet are based on our own knowledge on the date of the last version. Users must verify the suitability and thoroughness of provided information according to each specific use of the product.

This document must not be regarded as a guarantee on any specific product property.

The use of this product is not subject to our direct control; therefore, users must, under their own responsibility, comply with the current health and safety laws and regulations. The producer is relieved from any liability arising from improper uses.

Provide appointed staff with adequate training on how to use chemical products.



Data revisione 29/01/2016

Stampata il 10/10/2017

SAFETY DATA SHEET FOR SOLID COMPOUND

Pagina n. 12/12