

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: XYLENE THINNERS

CAS number: 1330-20-7

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.3. Details of the supplier of the safety data sheet

Company name: Rustins Ltd
Waterloo Road
Cricklewood
London
NW2 7TX
United Kingdom

Tel: +44 (0)208 450 4666

Fax: +44 (0)208 452 2008

Email: rustins@rustins.co.uk

1.4. Emergency telephone number

Emergency tel: .+44(0)2084504666 (Office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Skin Irrit. 2: H315; Acute Tox. 4: H312+332; Flam. Liq. 3: H226

Most important adverse effects: Flammable liquid and vapour. Harmful in contact with skin or if inhaled. Causes skin irritation.

2.2. Label elements

Label elements:

Hazard statements: H226: Flammable liquid and vapour.

H312+332: Harmful in contact with skin or if inhaled.

H315: Causes skin irritation.

Hazard pictograms: GHS02: Flame

GHS07: Exclamation mark



Signal words: Warning

SAFETY DATA SHEET

XYLENE THINNERS

Page: 2

Precautionary statements: P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P241: Use explosion-proof electrical/ventilating/lighting/.. equipment.
P260: Do not breathe vapours.
P280: Wear protective gloves/protective clothing/eye protection/face protection.
P302+352: IF ON SKIN: Wash with plenty of water/.
P361+364: Take off immediately all contaminated clothing and wash it before reuse.

2.3. Other hazards

Other hazards: In use, may form flammable / explosive vapour-air mixture.

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.1. Substances

Chemical identity: XYLENE

CAS number: 1330-20-7

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin.

Drench the affected skin with running water for 10 minutes or longer if substance is still on skin. Consult a doctor.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Do not induce vomiting. If conscious, give half a litre of water to drink immediately. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur. There may be vomiting.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

Section 5: Fire-fighting measures

[cont...]

SAFETY DATA SHEET

XYLENE THINNERS

Page: 3

5.1. Extinguishing media

Extinguishing media: Alcohol or polymer foam. Carbon dioxide. Dry chemical powder. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Flammable. In combustion emits toxic fumes. Forms explosive air-vapour mixture.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid. Eliminate all sources of ignition.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method. Do not use equipment in clean-up procedure which may produce sparks.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Avoid the formation or spread of mists in the air. Smoking is forbidden. Use non-sparking tools.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed. Keep away from sources of ignition. Prevent the build up of electrostatic charge in the immediate area. Ensure lighting and electrical equipment are not a source of ignition.

Suitable packaging: Must only be kept in original packaging.

[cont...]

SAFETY DATA SHEET

XYLENE THINNERS

Page: 4

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

XYLENE

Workplace exposure limits:

Respirable dust

| State | 8 hour TWA | 15 min. STEL | 8 hour TWA | 15 min. STEL |
|-------|-----------------------|-----------------------|------------|--------------|
| UK | 220 mg/m ³ | 441 mg/m ³ | - | - |

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Impermeable gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Impermeable protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Colourless

Odour: Pungent

Evaporation rate: No data available.

Oxidising: No data available.

Solubility in water: Insoluble

Also soluble in: Benzene.

Viscosity: Non-viscous

Boiling point/range°C: 137

Melting point/range°C: No data available.

Flammability limits %: lower: No data available.

upper: No data available.

Flash point°C: 23 - 55

Part.coeff. n-octanol/water: No data available.

Autoflammability°C: No data available.

Vapour pressure: No data available.

Relative density: 0.7800@ 20 C

pH: approx. 7

VOC g/l: 780

[cont...]

SAFETY DATA SHEET

XYLENE THINNERS

Page: 5

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions. Stable at room temperature.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat. Hot surfaces. Sources of ignition. Flames.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

XYLENE

| | | | | |
|-----|-----|------|------|-------|
| ORL | MUS | LD50 | 2119 | mg/kg |
| ORL | RAT | LD50 | 4300 | mg/kg |
| SCU | RAT | LD50 | 1700 | mg/kg |

Relevant hazards for product:

| Hazard | Route | Basis |
|-----------------------------|---------|-----------------------|
| Acute toxicity (ac. tox. 4) | INH DRM | Hazardous: calculated |
| Skin corrosion/irritation | DRM | Hazardous: calculated |

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur. There may be vomiting.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

[cont...]

SAFETY DATA SHEET

XYLENE THINNERS

Page: 6

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1307

14.2. UN proper shipping name

Shipping name: XYLENES

14.3. Transport hazard class(es)

Transport class: 3

14.4. Packing group

Packing group: III

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: Yes

[cont...]

SAFETY DATA SHEET

XYLENE THINNERS

Page: 7

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: D/E

Transport category: 3

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: H226: Flammable liquid and vapour.

H312+332: Harmful in contact with skin or if inhaled.

H315: Causes skin irritation.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.