

Blind rivet nut hand tool

GBM 50



Execution:

- Quick drill setup – fast and easy to drill into and drill out blind rivet nuts
- Ergonomic design, low effort, optimised leverage
- Sets blind rivet nuts up to M12
- Threaded mandrels and mouthpieces can be changed quickly and without tools

Delivery:

Set in a plastic carrying case with mouthpieces/threaded mandrels M5, M6, M8, M10, installation key and operating instructions

Art. no.	53195 303
Brand	GESIPA
Manufacturer Part Number	1619730
Model	GBM 50
Length	485 mm
Suitable for max. rivet diameter (rivet material: aluminium)	12 mm
Suitable for max. rivet diameter (rivet material: stainless steel)	10 mm
Gross Weight	3.500 kg
Product Group	561



EAN

4007081092487