

**RoHS
Compliant**



Features

- Glass passivated
- Surge overload rating -60 amperes peak
- Ideal for printed circuit board
- Plastic material has UL flammability classification 94V-0
- Mounting position : Any.
- Reverse Voltage: 50 Volts to 1000 Volts
- Forward Current: 2 Amperes

Maximum Ratings and Electrical Characteristics




Rating at 25°C ambient temperature unless otherwise specified.


Resistive or inductive load, 60Hz.

For capacitive load, derate current by 20%.

Characteristics	Symbol	KBP 2005G	KBP 201G	KBP 202G	KBP 204G	KBP 206G	KBP 208G	KBP 210G	Unit
Max. Recurrent Peak Reverse Voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Max. RMS Bridge Input Voltage	V_{RMS}	35	70	140	280	420	560	700	
Max. DC Blocking Voltage	V_{DC}	50	100	200	400	600	800	1000	
Max. Average Forward Rectified Current at $T_A = 50^\circ C$	$I_{(AV)}$	2							A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Super Imposed on Rated Load	I_{FSM}	60							
Max. Forward Voltage Drop Per Bridge Element at 2A Peak	V_F	1.1							V
Max. Reverse Current at Rated DC Blocking Voltage Per Element	I_R	10							μA
Max. Reverse Current at Rated DC Blocking Voltage Per Element at $T_J = 100^\circ C$		1							mA
Operating Temperature Range	T_J	-55 to +150							$^\circ C$
Storage Temperature Range	T_{STG}								


Rating and Characteristic Curves





Diagram

KBP



Dimensions : Inches (Millimetres)

Part Number Table

Description	Part Number
Bridge Rectifier Diode, Single Phase, 50V, 2A	KBP2005G
Bridge Rectifier Diode, Single Phase, 100V, 2A	KBP201G
Bridge Rectifier Diode, Single Phase, 200V, 2A	KBP202G
Bridge Rectifier Diode, Single Phase, 400V, 2A	KBP204G
Bridge Rectifier Diode, Single Phase, 600V, 2A	KBP206G
Bridge Rectifier Diode, Single Phase, 800V, 2A	KBP208G
Bridge Rectifier Diode, Single Phase, 1kV, 2A	KBP210G

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.