

tesa® 4330

High performance paper masking tape for paintworks with oven drying up to 140 °C

PRODUCT INFORMATION

Product Description

tesa® 4330 is a finely crêped, flexible, wet resistant masking tape with a high tensile strength.

Main Application

Further applications are e.g.

- masking of circuit boards before plating
- cable bundling
- packaging

Technical Data

■ Backing material	slightly-creped paper	■ Elongation at break	12 %
■ Total thickness	175 µm	■ Tensile strength	42 N/cm
■ Type of adhesive	natural rubber	■ Temperature resistance	140 °C
■ Adhesion to steel	4.8 N/cm		

Properties

■ Hand tearability	++	■ Sharp colour edge	+
■ Easy to remove	yes	■ Conformability	+
■ Paint anchorage	++		

Evaluation across relevant tesa® assortment: ++ very good, + good, o medium, - low

Additional Info

This tape guarantees sharp edged finishing due to its fine crêped structure. The adhesion of paint and filler to the reverse side of the tape is excellent.

tesa® 4330 can be removed very easily without tearing any residues.

tesa® 4330 is also available for converting/die-cutting with a paper liner (4330 PV1).

For latest information on this product please visit <http://1.tesa.com/?ip=04330>

Page 1 of 1 / As of 12/08/13