

## Fixed centring point

With half and flattened point



### Application:

For centring and supporting long and narrow workpieces on lathes and grinding machines.

### Execution:


- Tip angle 60°.
- Taper hardened and precision-ground.
- Carbide-tipped.
- Concentricity tolerance on cemented carbide  $\leq 0.8 \mu\text{m}$ .

### Advantage:

- Very good accessibility to workpieces.
- Wear-resistant carbide tip.

### Delivery:

1x centring point MK 1.



<b>Art. no.</b>	<b>22113 030</b>
<b>Brand</b>	BRUCKNER
<b>Manufacturer Part Number</b>	2813H
<b>Morse taper size</b>	MK 3
<b>Programming size</b>	44 mm
<b>Diameter of flat area</b>	11 mm
<b>Length of flat area</b>	38 mm
<b>Height of flat area</b>	6 mm
<b>Concentricity tolerance</b>	0.008 mm
<b>DIN</b>	806
<b>Gross Weight</b>	0.438 kg
<b>Product Group</b>	2AA