

electronic dial gauge

1075 R



Application:

For static measurements of lengths and length differences

Execution:

- zero setting at any position
- large LCD display (12 mm)
- reference system
- mm/inch changeover

Advantage:

- LOCK function (key lock)
- Switched on by the ON button or automatically switched on by moving the button
- particularly energy-saving electronics (battery lifetime up to 3 years)



| | |
|---|-------------------|
| Art. no. | 33167 520 |
| Brand | MAHR |
| Manufacturer Part Number | 4336030 |
| Length measuring range | 12.5 mm |
| Digit increment | 0.001 |
| Min./max. measurement force | 0.5-1 N |
| Data transmission type | multiCOM |
| IP protection class | IP 52 |
| Absolute function | Yes |
| Automatic switch-off | Yes |
| Preset function | Yes |
| Number of rechargeable batteries/batteries | 1 PCS |
| Rechargeable battery/battery capacity | 200 mAh |
| Battery voltage | 3 V |
| Weight of rechargeable battery/battery | 0.003 kg |
| Battery designation | 3V CR2032 Lithium |
| Reversible counting direction | Yes |
| Calibration Group Description | Dial gauge |
| Calibration Group | CE |
| Gross Weight | 0.273 kg |
| Product Group | 305 |

EAN

4059192014322