

Dial gauge with magnetic back

Application:

For measuring lengths and length differences, e.g. concentricity, flatness, positional measurements.

Execution:

- Measuring pin and clamping shaft made from durable stainless steel

Advantage:

- Back wall is designed as magnetic clamp (detachable)
- Can be used without stand
- The magnet does not affect dial gauge function

Delivery:

In a case



Art. no.	33100 020
Brand	HK
Manufacturer Part Number	33100020
Length measuring range	3 mm
Scale value	0.01 mm
Measurement travel of one pointer revolution	0.5 mm
Outer diameter	40 mm
Material of outer ring	Plastic
Measurement force	1 N
DIN	878
Calibration Group	CE
Gross Weight	0.050 kg
Product Group	331

EAN

4039247207312