

## Pneumatic straight grinder G 232 H

**MANNESMANN  
DEMAG**

### Application:

For heavy deburring work as well as high-precision milling, grinding and roughing

### Delivery:

Includes hose unit and collet chuck keys



<b>Art. no.</b>	<b>75061 080</b>
<b>Brand</b>	MANNESMANN DEMAG
<b>Manufacturer Part Number</b>	29935255
<b>Model</b>	G 232 H
<b>Valve design</b>	Lever valve
<b>Max. idle speed</b>	25000 rpm
<b>Min./max. idle speed</b>	0-25000 rpm
<b>Power output</b>	440 W
<b>Air consumption</b>	12 l/s
<b>Connection thread</b>	G 1/4 inch
<b>Sound-pressure level</b>	76 dB
<b>Length</b>	180 mm
<b>Diameter of housing</b>	39 mm
<b>Collet chuck diameter</b>	6 mm
<b>Suitable for max. sanding block diameter</b>	24 mm
<b>Max. HM rotating milling cutter diameter</b>	12 mm
<b>Weight</b>	0.74 kg
<b>Gross Weight</b>	1.810 kg
<b>Product Group</b>	7AA

### EAN

4251757300325