

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH)

Date of issue: 11/26/2018 Revision date: 11/26/2018 Supersedes: 7/21/2016 Version: 3.01

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name : Saniwip®

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Use of the substance/mixture : Skin protecting agent

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Supplier Email competent person

Peter Greven Physioderm GmbH sds@kft.de

Procter-&-Gamble-Str. 26

53881 Euskirchen - Deutschland

T +49 02251 77617 - 0 - F +49 (02251) 77617 - 44

1.4. Emergency telephone number

Emergency number : National Health Service (NHS)

24 hour national number consumer

England and Scotland: 111

Wales: 0845 46 47

Northern Ireland: call your local General Practitioner

Call 999 if there is a life-threatening incident.

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

Adverse physicochemical, human health and environmental effects

Cosmetic product. If used as specified, no specific risks are known.

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Extra phrases : The product is subject of the Regulation 1223/2009 for cosmetics in its current version.

2.3. Other hazards

This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Comments : W/O emulsion based on water and lipids with possibly fillers, preservatives, fragrance

and other means

This mixture does not contain any substances to be mentioned according to the criteria of section 3.2 of REACH annex II

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general : In all cases of doubt, or when symptoms persist, seek medical attention.

First-aid measures after inhalation : Inhalation of product is unlikely.

GB - en 1/6

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH)

First-aid measures after skin contact : No specific measures are necessary.

First-aid measures after eye contact : Rinse eyes with water as a precaution.

First-aid measures after ingestion : Rinse mouth out with water. Call a poison center or a doctor if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

No additional information available

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Water spray. Dry powder. Foam. Carbon dioxide. Use fire fighting measures suiting the

environment.

Unsuitable extinguishing media : Strong water jet.

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire : Toxic fumes may be released. Carbon monoxide. Carbon dioxide. Sulphur oxides.

5.3. Advice for firefighters

Firefighting instructions : Cool closed containers exposed to fire with water spray.

Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained

breathing apparatus. Complete protective clothing.

Other information : Do not allow run-off from fire fighting to enter drains or water courses. Disposal must be

done according to official regulations.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures : Avoid contact with eyes. Spill area may be slippery.

6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information

refer to section 8: "Exposure controls/personal protection".

6.2. Environmental precautions

Avoid sub-soil penetration.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Collect spillage. Clean contaminated surfaces with an excess of water.

Other information : Disposal must be done according to official regulations.

6.4. Reference to other sections

Information for safe handling. See section 7. Concerning personal protective equipment to use, see section 8. For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : No specific measures are necessary.

Hygiene measures : Do not eat, drink or smoke when using this product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Store at room temperature. Store in a dry place. Containers which are opened should be

properly resealed and kept upright to prevent leakage.

Information about storage in one common storage

facility

: Keep away from food, drink and animal feeding stuffs.

7.3. Specific end use(s)

No additional information available.

GB - en 2/6

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH)

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

No additional information available

8.2. Exposure controls

Hand protection:

Not required

Eye protection:

Not required for normal conditions of use

Skin and body protection:

Not required

Respiratory protection:

Not required

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state : Liquid Appearance : Cream. Colour : white. Odour : unperfumed. Odour threshold : No data available pΗ : No data available Relative evaporation rate (butylacetate=1) : No data available Melting point : Not applicable Freezing point : No data available : No data available Boiling point Flash point : No data available Auto-ignition temperature : No data available Decomposition temperature : No data available Flammability (solid, gas) : Not applicable Vapour pressure : No data available Relative vapour density at 20 °C : No data available : No data available Relative density Density : 0.971 - 1.001 g/cm3 Solubility : Water: Not miscible Log Pow : No data available Viscosity, kinematic : No data available Viscosity, dynamic : No data available

Oxidising properties : Non oxidizing.

Explosive limits : No data available

9.2. Other information

Explosive properties

Other properties : No additional information available.

: Product is not explosive.

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions. To avoid thermal decomposition, do not overheat.

GB - en 3/6

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH)

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

No additional information available

10.5. Incompatible materials

No additional information available

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral) : Not classified (Based on available data, the classification criteria are not met) : Not classified (Based on available data, the classification criteria are not met) Acute toxicity (dermal) Acute toxicity (inhalation) : Not classified (Based on available data, the classification criteria are not met) : Not classified (Based on available data, the classification criteria are not met) Skin corrosion/irritation Serious eye damage/irritation : Not classified (Based on available data, the classification criteria are not met) : Not classified (Based on available data, the classification criteria are not met) Respiratory or skin sensitisation Germ cell mutagenicity : Not classified (Based on available data, the classification criteria are not met) Carcinogenicity : Not classified (Based on available data, the classification criteria are not met) : Not classified (Based on available data, the classification criteria are not met) Reproductive toxicity STOT-single exposure : Not classified (Based on available data, the classification criteria are not met) STOT-repeated exposure : Not classified (Based on available data, the classification criteria are not met) Aspiration hazard : Not classified (Based on available data, the classification criteria are not met)

SECTION 12: Ecological information

12.1. Toxicity

Acute aquatic toxicity : Not classified (Based on available data, the classification criteria are not met)
Chronic aquatic toxicity : Not classified (Based on available data, the classification criteria are not met)

12.2. Persistence and degradability

No additional information available

12.3. Bioaccumulative potential

No additional information available

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

Saniwip®

This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII

This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII

12.6. Other adverse effects

Other adverse effects : No additional information available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste treatment methods : Disposal must be done according to official regulations. European waste catalogue.

Product/Packaging disposal recommendations : Recycle or dispose of in compliance with current legislation.

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

GB - en 4/6

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH)

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.2. UN proper shippin	g name			
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.3. Transport hazard	class(es)			
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.4. Packing group				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.5. Environmental haz	zards			
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
No supplementary information	on available			

14.6. Special precautions for user

Overland transport

Not applicable

Transport by sea

Not applicable

Air transport

Not applicable

Inland waterway transport

Not applicable

Rail transport

Not applicable

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Other information, restriction and prohibition regulations

: The product is subject of the Regulation 1223/2009 for cosmetics in its current version.

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Indication of changes:					
Section	Changed item	Change	Comments		
	General revision				

GB - en 5/6



Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH)

Abbreviations and acron	yms:	
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Water	
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road	
ATE	Acute Toxicity Estimate	
BCF	Bioconcentration factor	
CLP	Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008	
DMEL	Derived Minimal Effect level	
DNEL	Derived-No Effect Level	
DPD	Dangerous Preparations Directive 1999/45/EC	
DSD	Dangerous Substances Directive 67/548/EEC	
EC50	Median effective concentration	
IARC	International Agency for Research on Cancer	
IATA	International Air Transport Association	
IMDG	International Maritime Dangerous Goods	
LC50	Median lethal concentration	
LD50	Median lethal dose	
LOAEL	Lowest Observed Adverse Effect Level	
NOAEC	No-Observed Adverse Effect Concentration	
NOAEL	No-Observed Adverse Effect Level	
NOEC	No-Observed Effect Concentration	
OECD	Organisation for Economic Co-operation and Development	
PBT	Persistent Bioaccumulative Toxic	
PNEC	Predicted No-Effect Concentration	
REACH	Registration, Evaluation, Authorisation and Restriction of Chemicals Regulation (EC) No 1907/2006	
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail	
SDS	Safety Data Sheet	
STP	Sewage treatment plant	
TLM	Median Tolerance Limit	
vPvB	Very Persistent and Very Bioaccumulative	
Data sources	: MSDSs of the suppliers. Information provided by the manufacturer.	

Data sources : MSDSs of the suppliers. Information provided by the manufacturer.

Department issuing data specification sheet:

: KFT Chemieservice GmbH

Im Leuschnerpark. 3 64347 Griesheim

Postfach 1451 64345 Griesheim

Germany

Phone: +49 6155-8981-400 Fax: +49 6155 8981-500

Safety Data Sheet Service: +49 6155 8981-522

Contact person : Stefanie Zgorzelski

KFT SDS EU 00

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product

GB - en 6/6