

## T-slot bolts



### Application:

For clamping workpieces on machine tables.

### Execution:

- Tempered
- Rolled thread
- Forged
- With milled groove guide
- M8 to M12, strength class 10.9
- M16 to M24, strength class 8.8
- DIN 787



<b>Art. no.</b>	<b>26200 345</b>
<b>Brand</b>	AMF
<b>Manufacturer Part Number</b>	8 1505
<b>DIN</b>	787
<b>Thread dimension</b>	M12
<b>Groove width</b>	12 mm
<b>Length excluding head</b>	160 mm
<b>Outer diameter</b>	11.7 mm
<b>Thread length</b>	100 mm
<b>Length of head</b>	18 mm
<b>Head height</b>	7 mm
<b>Gross Weight</b>	0.187 kg
<b>Product Group</b>	260

### EAN

4020772081508