




# BMP<sup>®</sup>51 & BMP<sup>®</sup>53 LABEL MATERIALS

## BMP<sup>®</sup>51 AND BMP<sup>®</sup>53 ROUGH SURFACE LABELS FOR PRODUCT ID: B-422 GLOSS POLYESTER

Ideal for marking texturized or rough surfaces.



Part No.	Diagram	Reference	Material	Dimensions A (mm)	B (mm)	Labels per Cartridge	Colour
143239	Fig. 33	MC-375-422	B-422	9.53	7.60m	1 (cont.)	Black on White
143240	Fig. 33	MC-475-422	B-422	12.07	7.60m	1 (cont.)	Black on White
143241	Fig. 29	M-7-422	B-422	12.70	12.70	280	Black on White
143242	Fig. 33	MC-500-422	B-422	12.70	7.60m	1 (cont.)	Black on White
131592	Fig. 29	M-47-422	B-422	25.40	12.70	360	Black on White
131608	Fig. 29	M-49-422	B-422	25.40	25.40	200	Black on White
131595	Fig. 33	MC1-1000-422	B-422	25.40	7.60m	1 (cont.)	Black on White
131576	Fig. 29	M-90-422	B-422	38.10	19.05	200	Black on White
131577	Fig. 29	M-89-422	B-422	38.10	12.70	360	Black on White




## BMP<sup>®</sup>51 AND BMP<sup>®</sup>53 LOW SURFACE ENERGY / POWDER COATED SURFACE LABELS FOR PRODUCT ID: B-483 ULTRA AGGRESSIVE POLYESTER

Adheres to difficult low-surface energy items such as PVC piping, powder coated surfaces, blow-molded equipment cases, ABS and recycled plastics.




Part No.	Diagram	Reference	Material	Dimensions A (mm)	B (mm)	Labels per Cartridge	Colour
131605	Fig. 29	M-47-483	B-483	25.40	12.70	360	Black on White
131599	Fig. 29	M-60-483	B-483	50.80	25.40	80	Black on White
143304	Fig. 29	M-61-483	B-483	50.80	12.70	80	Black on White




## BMP<sup>®</sup>51 AND BMP<sup>®</sup>53 RATING PLATE LABELS FOR PRODUCT ID: B-428 METALLIZED POLYESTER

Create serial or rating plates with barcodes, graphics and more. Has a metal looking finish.




Part No.	Diagram	Reference	Material	Dimensions A (mm)	B (mm)	Labels per Cartridge	Colour
133064	Fig. 46	M-92-428-BB	B-428	28.70	12.70	360	Black on Silver
143278	Fig. 29	M-29-428	B-428	38.10	12.70	360	Black on Silver
143279	Fig. 29	M-30-428	B-428	38.10	19.10	260	Black on Silver
131603	Fig. 29	M-60-428	B-428	50.80	25.40	80	Black on Silver



## BMP<sup>®</sup>51 AND BMP<sup>®</sup>53 SAFETY & FACILITY ID MATERIALS: BIN, STORAGE, & GENERAL INDUSTRIAL ID

Choose from several materials with aggressive adhesives for use in commercial/industrial applications, including low surface energy and textured surfaces.

Part No.	Diagram	Reference	Material	Dimensions A (mm)	B (mm)	Labels per Cartridge	Colour
<b>B-422 Gloss Polyester Material</b>							
143241	Fig. 29	M-7-422	B-422	12.70	12.70	280	Black on White
131592	Fig. 29	M-47-422	B-422	25.40	12.70	360	Black on White
131608	Fig. 29	M-49-422	B-422	25.40	25.40	200	Black on White
131577	Fig. 29	M-89-422	B-422	38.10	12.70	360	Black on White
131576	Fig. 29	M-90-422	B-422	38.10	19.05	200	Black on White
<b>B-483 Ultra Aggressive Polyester Material</b>							
131605	Fig. 29	M-47-483	B-483	25.40	12.70	360	Black on White
143304	Fig. 29	M-61-483	B-483	50.80	12.70	80	Black on White
131599	Fig. 29	M-60-483	B-483	50.80	25.40	80	Black on White
<b>B-499 Nylon Cloth Material</b>							
143352	Fig. 29	M-11-499	B-499	19.05	12.70	220	Black on White
143353	Fig. 29	M-84-499	B-499	22.86	12.70	200	Black on White
143362	Fig. 29	M-132-499	B-499	38.10	31.75	160	Black on White
131600	Fig. 29	M-128-499	B-499	48.26	25.40	100	Black on White



Refer to the material guide on page 397-403 for full material specifications and descriptions.