

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

RINGS

Stainless steel.

BALL CHAINS

Nickel-plated brass.



FEATURES AND APPLICATIONS

GN 111 ball chains are mainly used together with the different types of lock pins.

The ball chain main feature is the flexibility.



Application example



Code	Description	d1	d2	l	Static load with ring [N]	Static load without ring [N]	⚖️
GN.10881	GN 111-200-14	14*	1	200	50	180	100
GN.10882	GN 111-200-18	18**	1.3	200	90	180	100
GN.11506	GN 111-200-24	24	1.5	200	100	180	100
GN.11507	GN 111-200-30	30	1.8	200	120	180	100
GN.10884	GN 111-320-14	14*	1	320	50	180	100
GN.10885	GN 111-320-18	18**	1.3	320	90	180	100
GN.11508	GN 111-320-24	24	1.5	320	100	180	150
GN.11509	GN 111-320-30	30	1.8	320	120	180	150
GN.10887	GN 111-500-14	14*	1	500	50	180	150
GN.10888	GN 111-500-18	18**	1.3	500	90	180	150
GN.11510	GN 111-500-24	24	1.5	500	100	180	200
GN.11511	GN 111-500-30	30	1.8	500	120	180	200
GN.10901	GN 111-1000-14	14*	1	1000	50	180	300
GN.10902	GN 111-1000-18	18**	1.3	1000	90	180	300
GN.10903	GN 111-1000-24	24	1.5	1000	100	180	300
GN.10904	GN 111-1000-30	30	1.8	1000	120	180	300

* Suitable for the following lock pins: GN 124 only Ø6, Ø8; GN 113.1, GN 113.3, GN 113.5, GN 113.6, GN 113.7, GN 113.8, GN 114.2, GN 114.3, GN 114.6 all the Ø.

** Suitable for the following lock pins: GN 124 only Ø10, Ø12, Ø16.

Indexing and positioning elements