

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

| REVISIONS | | | DOC. NO | I. SPC-F005 | * Effe | ctive: 7/8/ | ,05 * D | CP No: 1398 |
|-----------|-----|----------------------|---------|-------------|--------|-------------|---------|-------------|
| DCP # | RE∨ | DESCRIPTION | DRAWN | DATE | CHECKD | DATE | APPR∨I | DATE |
| XX | XX | xxxx | xxxx | 08-08-08 | xxxx | 08-08-08 | xxxx | 08-08-08 |
| 2067 | В | Listing Info Updated | JN | 08-14-09 | JN | 08-14-09 | JN | 08-14-09 |


MATERIAL

2. Material

2-1. Frame : DIE-CAST ALUMINUM

2-2. Impeller : PC of UL 94V-0

2-3. Lead Wire : UL1007, 18 awg, BLACK



Air Flow Direction: Toward lable side.

TOLERANCES:

Units:mm



| DISCLA | AIMER: |
|--------|--------|
| | |

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

| UNLESS OTHERWISE |
|------------------|
| SPECIFIED, |
| DIMENSIONS ARE |
| FOR REFERENCE |
| PURPOSES ONLY. |

| DRAWN BY: | DATE: |
|--------------|----------|
| XXXX | 08-08-08 |
| CHECKED BY: | DATE: |
| XXXX | 08-08-08 |
| APPROVED BY: | DATE: |
| XXXX | 08-08-08 |

| DRAW | 'ING TITLE: | | | | | | |
|--------------|-------------|-----|---------------------|------|-----------|------|-----|
| Axial Ac Fan | | | | | | | |
| SIZE | DWG. N□. | | | ELEC | TRONIC FI | LE | RE∨ |
| Α | | MC2 | 21674 | 14 | lМ9030. | dwg | Α |
| SCALE: NTS | | | U.D.M.: INCHES [mm] | | SHEET: | 1 OF | 1 |

CHARACTERISTICS

1. Motor Design : Reliable Alveolate Motor Construction.

2. Insulation Resistance : 500 Megohms minimum at 500 VDC.

3. Dielectric Strength : 1800 VAC for one second.

4. Motor Protection : Thermal protected & Class B(II)

5. Noise Level : Measured in a semi-anechoic chamber

with background noise level below 15

dB(A). The fan is running in free air with the

microphone at a distance of one meter

from the fan intake.

6. Tolerance : $\pm 15\%$ on rated power and current.


7. Air Performance : Measured by a double chamber. The values

are recorded when the fan speed has stabilized

at rated voltage.



| ALL RIGHTS RESERVED, NO PORTION OF THIS PUBLICATION, WHE | RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT | | DWG, N□, | | ELECT | RUNIC FILE | | REV | |
|--|--|-------|----------|---------------------|-------|------------|------|-----|--|
| THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. | | A | MC | 21674 | | 14M9030 | | | |
| SPC-F005.DWG | DDC. ND. SPC-F005 * Effective 7/8/02 * DCP No 1398 | SCALI | E: NTS | U.□.M.: Millimeters | | SHEET: 2 | OF 4 | 4 | |





| ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. | | SIZE | DWG. N□. | | ELEC. | TRONIC FILE | | RE∨ |
|---|---|------|----------|---------------------|-------|-------------|----|-----|
| | | A | MC | 21674 | | 14M9030 | | |
| SPC-F005.DWG | DDC. ND. SPC-F005 * Effective 7/8/02 * DCP No: 1398 | SCAL | E: NTS | U.□.M.: Millimeters | | SHEET: 3 | ΟF | 4 |

SPECIFICATIONS

1-1. Rated Voltage : 115 VAC 50/60 Hz

1-2. Operating Voltage Range : 75~125 VAC

1-3. Starting Voltage : 75 VAC (25 deg. C POWER ON/OFF)

1-4. Rated Speed : 2800/3200 RPM ± 10%

1-5. Air Delivery : 203/239 CFM

1-6. Static Pressure : 0.62/0.69 Inch-HOO

1-7. Rated Current : 0.22/0.23 AMP

1-8. Rated Power : 25/27 WATTS

1-9. Noise Level : 51/58 dB(A)

1-10. Direction of Rotation : clockwise viewed from front of fan blade

1-11. Operating Temperature : -10 to +70 deg.C

1-12. Storage Temperature : -40 to +70 deg.C

1-13. Bearing System : Precision ball bearing system

1-14. Weight : 908 g

1-15. Safety : UL/CUR Approvals

1-16. Vibration : Vibration of acceleration 1.5G and

frequency 5~50~5Hz is applied in all 3 directions(X,Y,Z), in cycles of 1 minute each,

for a total vibration time of 30 minutes.



| ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT | | | SISF | DWG. NU. | | FLEC | IRUNIC FILE | | REV | ı |
|--|--|--|-------|----------|---------------------|------|-------------|------|-----|---|
| | THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. | | Α | MC: | 21674 | | 14M9030 | | | ĺ |
| | SPC-F005.DWG | DDC. ND. SPC-F005 * Effective: 7/8/02 * DCP No: 1398 | SCALI | E: NTS | U.□.M.: Millimeters | | SHEET: 4 | . OF | 4 | |