Printed circuit mount - 3 mm contact gap 50 A Power relay for photovoltaic inverters

- 2 and 3 pole versions (NO, double break
- Contact gap ≥ 3 mm (according to VDE 0126-1-1, EN 62109-1, EN 62109-2)
- DC coils, with only 170 mW holding power
- Reinforced insulation between coil and contacts
- 1.5 mm gap between PCB and relay base
- Suitable for use at ambient temperatures up to 85 °C (with energy-saving coil energization) or 70 °C (with standard coil energization)
- Meets the EN 60335-1 requirements of resistance to heat and fire (GWIT 775 $^{\circ}\text{C}$ and GWFI 850 °C)
- Cadmium free contact materials:
- AgNi version (for applications where lower contact resistance is needed)
- AgSnO₂ version (for applications where higher inrush current values are expected)










- Contact gap ≥ 3 mm
- PCB mount








finder

- 3 NO
- Contact gap ≥ 3 mm
- PCB mount









For earlier description of the control of the contr			Common didention	
For outline drawing see page 6		Copper side view	Copper side view	
Contact specification				
Contact configuration		2 NO (DPST-NO)	3 NO (3PST-NO)	
Contact gap		≥ 3	≥ 3	
Rated current/				
Maximum peak current (for 5 ms)	Α	50/150	50/150	
Rated voltage/	V/ A C	400/600	400/500	
Maximum switching voltage	V AC	400/690	400/690	
Rated load AC1/AC7a (per pole)	VA	20000	20000	
Rated load AC15 (per pole @ 230 V AC)	VA	2300	2300	
Single-phase motor rating (230 V AC)	kW	2.2	2.2	
Three-phase motor rating (480 V AC)	kW	_	11	
Breaking capacity DC1: 24/110/220 V	Α	50/4/1	50/4/1	
Minimum switching load mV	V (V/mA)	1000 (10/10)	1000 (10/10)	
Standard contact material		AgSnO₂	AgSnO ₂	
Coil specification				
Nominal voltage (U _N)	V DC	5 - 6 - 8 - 12 - 24	4 - 48 - 60 - 110	
Rated power		1.7	1.7	
Operating range (-40+70)°C	DC	(0.901.1)U _N	(0.901.1)U _N	
Energy-saving mode (-40+85)°C				
Operating range for 1 s		(0.952.5)U _N	(0.952.5)U _N	
Holding voltage range	DC	(0.320.65)U _N	(0.320.65)U _N	
Minimum holding powe	r W	0.17	0.17	
Must drop-out voltage	DC	0.05 U _N	0.05 U _N	
Technical data				
Mechanical life	cycles	1 · 10 ⁶	1 · 10 ⁶	
Electrical life at rated load AC7a	cycles	30 · 10 ³	30 · 10 ³	
Operate/release time	ms	25/5	25/5	
Ambient temperature range				
(energy-saving mode)	°C	-40+70 (-40+85)	-40+70 (-40+85)	
Environmental protection		RT II	RT II	

www.findernet.com

Approvals (according to type)



Printed circuit mount - 5.2 mm contact gap 50 A Power relay for photovoltaic inverters

- 2 and 3 pole versions (NO double break
- Contact gap \geq 5.2 mm (according to VDE 0126-1-1, EN 62109-1, EN 62109-2)
- Suitable for inverters with DC input up to 1500 V and AC output up to 690 V, installations up to 4000 m above sea level
- DC coils, with only 170 mW holding power
- Reinforced insulation between coil and contacts
- 1.5 mm gap between PCB and relay base
- Suitable for use at ambient temperatures up to 85 °C (with energy-saving coil energization) or 60 °C (with standard coil energization)
- Meets the EN 60335-1 requirements of resistance to heat and fire (GWIT 775 °C and GWFI 850 °C)
- Cadmium free contact materials:
- AgNi version (for applications where lower contact resistance is needed)
- AgSnO₂ version (for applications where higher inrush current values are expected)









- 2 NO
- Contact gap \geq 5.2 mm
- PCB mount






- 3 NO
- Contact gap ≥ 5.2 mm
- PCB mount









For	outline	drawing	see	page 6	

or outline drawing see page 6		Copper sid
ontact specification		
ontact configuration		2 NO (DPS
Contact gap	mm	≥ 5.2

Rated current/		
Maximum peak current (for 5 ms)	Α	
Rated voltage/		
Maximum switching voltage	V AC	
Rated load AC1/AC7a (per pole)	VA	
Rated load AC15 (per pole @ 230 V AC)	VA	
Single-phase motor rating (230 V AC)	L\\/	

	Holding voltage range	DC	
	Minimum holding power	W	
Must drop-out v	DC		
Technical data			
Mechanical life	cycles		
Electrical life at	cycles		
Operate/release	time	ms	

Environr Approvals (according to type)

Copper	side view

ide view	Copper side view


EFIE @ cAL®us &

Contact specification			
Contact configuration	2 NO (DPST-NO)	3 NO (3PST-NO)	
Contact gap m	n ≥ 5.2	≥ 5.2	
Rated current/			
Maximum peak current (for 5 ms)	A 50/150	50/150	
Rated voltage/			
Maximum switching voltage V A		400/690	
Rated load AC1/AC7a (per pole)	A 20000	20000	
Rated load AC15 (per pole @ 230 V AC)	A 2300	2300	
Single-phase motor rating (230 V AC) k	V 2.2	2.2	
Three-phase motor rating (480 V AC)	V	11	
Breaking capacity DC1: 24/110/220	A 50/7/2	50/7/2	
Minimum switching load mW (V/m/	1000 (10/10)	1000 (10/10)	
Standard contact material	AgSnO ₂	AgSnO ₂	
Coil specification			
Nominal voltage (U_N) V D	5 - 6 - 8 - 12 - 24 - 48 - 60 - 110		
Rated power	V 2.7	2.7	
Operating range (-40+60)°C	(0.901.1)U _N	(0.901.1)U _N	
Energy-saving mode (-40+85)°C			
Operating range for 1 s	(0.952.5)U _N	(0.952.5)U _N	
Holding voltage range	(0.250.5)U _N	(0.250.5)U _N	
Minimum holding power	V 0.17	0.17	
Must drop-out voltage	0.05 U _N	0.05 U _N	
Technical data			
Mechanical life cycle	s 1 · 10 ⁶	1 · 10 ⁶	
Electrical life at rated load AC7a cycle	s 30 · 10 ³	30 · 10 ³	
Operate/release time	s 30/4	30/4	
Ambient temperature range			
(energy-saving mode)	-40+60 (-40+85)	-40+60 (-40+85)	
Environmental protection	RT II	RT II	



Ordering information

Example: 67 series solar relay, single PCB terminals, 2 pole NO, \geq 3 mm contact gap.



Technical data

Insulation according to EN 61810	-1				
Nominal voltage of supply system		V AC	400/690 3-phase	400 1-phase	230/400
Rated insulation voltage		V AC	630	400	400
Pollution degree		3			
Insulation between coil and conta	act set				
Type of Insulation			Reinforced		
Overvoltage category			III		
Rated impulse voltage	kV (1	1.2/50 μs)	6		
Dielectric strength		V AC	4000		
Insulation between adjacent cont	tacts				
Type of Insulation			Basic		
Overvoltage category			III		
Rated impulse voltage	kV (1.2/50)µs	6		
Dielectric strength V AC			2500		
Insulation between open contact	s				
Type of disconnection			Micro-disconnection*	:	Full-disconnection
Overvoltage category			_		III
Rated impulse voltage	kV (1.2/50)µs	_		4
Dielectric strength		V AC	2500 (67.xx-x300)/3000 (67.xx-x500)		
Conducted disturbance immunity	,				
Burst (550)ns, 5 kHz, on A1 - A2			EN 61000-4-4		level 4 (4 kV)
Surge (1.2/50 μs) on A1 - A2 (differe	ntial mode)		EN 61000-4-5		level 4 (4 kV)
Other data					
Bounce time: NO		ms	2		
Vibration resistance (10150)Hz: N	0	g	15		
Shock resistance		g	35		
Power lost to the environment	without contact current	W	1.7 (67.xx-x300)/2.7 (67.xx-x500)		
	with rated current	W	8.5 (67.xx-x300)/9.5 (6	57.xx-x500)	
Recommended distance between re	elays mounted on PCB	mm	≥ 20		
Short circuit protection					
Rated conditional short circuit curre	ent	kA	5		
Back-up fuse for motor load		Α	30 (delayed type)		




Contact specification

F 67 - Electrical life vs contact current (AC1/AC7a load)


10⁶
10⁵
10⁵
10⁶
10⁶
10 20 30 40 50 (A)

H 67 - Maximum DC breaking capacity (67.xx-x300)




When switching a resistive (DC1) or inductive (DC13) load having voltage and current values under the corresponding curve, an electrical life of > 30000 cycles can be expected.

H 67 -Maximum DC breaking capacity (67.xx-x500)



When switching a resistive (DC1) or inductive (DC13) load having voltage and current values under the corresponding curve, an electrical life of > 30000 cycles can be expected.

Connection of contacts in parallel



Connecting in parallel the contacts, with appropriate dimensioning of tracks on PC board, allow the relays to carry and switch loads up to 100 A:

- 100 A, with 67.23...4300S version
- 80 A, with 67.23...1300 version

Coil specifications


DC coil data, 67.xx-x300

Nominal voltage	Coil code	Operating range (@ 70 °C max)		Holding voltage	Resistance	Rated coil consumption I at U _N
U _N		U_{min}	U _{max}	U _h	R	I _N
V		V	V	V	Ω	mA
5	9 .005	4.5	5.5	1.6	14.7	340
6	9 .006	5.4	6.6	1.9	21.5	279
8	9 .008	7.2	8.8	2.6	37.6	213
12	9 .012	10.8	13.2	3.8	85	141
24	9 .024	21.6	26.4	7.7	340	71
48	9 .048	43.2	52.8	15.4	1355	35
60	9 .060	54	66	19.2	2120	28
110	9 .110	99	121	35.2	7120	15

DC coil data, 67.xx-x500

Nominal voltage	Coil code	Operating range (@ 60 °C max)		Holding voltage	Resistance	Rated coil consumption I at U _N
U _N		U _{min}	U _{max}	U _h	R	I _N
V		V	V	V	Ω	mA
5	9 .005	4.5	5.5	1.25	9.3	538
6	9 .006	5.4	6.6	1.5	13.5	444
8	9 .008	7.2	8.8	2	23.7	338
12	9 .012	10.8	13.2	3	53.5	224
24	9 .024	21.6	26.4	6	213	113
48	9 .048	43.2	52.8	12	855	56
60	9 .060	54	66	15	1335	45
110	9 .110	99	121	27.5	4500	24

R 67 - Operating range v ambient temperature, 67.xx-x300 with standard (continuous) coil energization (-40...+70)°C



- 1 Max. permitted coil voltage.
- 2 Min. pick-up voltage with coil at ambient temperature.


Energy saving mode

In some applications, such as photovoltaic inverters, it may be necessary to minimize the overall relay power dissipation and to permit use at higher ambient temperature levels (up to 85 °C). This can be achieved by initially applying a coil voltage within the Energy saving mode Operating range (see diagram to the right) and then rapidly (< 1 s) reducing the coil voltage to a level within the Holding voltage range. The lower the Holding voltage, the lower is the continuous power dissipation of the coil (0.17 W minimum).

Coil voltages as high as $2.5 \, U_N$ may be used, when necessary, to reduce the contact operate time.


R 67 - Operating range v ambient temperature, 67.xx-x500 with standard (continuous) coil energization (-40 ±60)°

with standard (continuous) coil energization (-40...+60)°C



- 1 Max. permitted coil voltage.
- 2 Min. pick-up voltage with coil at ambient temperature.

R 67 - Operating range v ambient temperature, 67.xx-x300/x500 in energy saving mode (-40...+85)°C



- 1 Max. permitted coil voltage.
- 2 Min. pick-up voltage with coil at ambient temperature.





Outline drawings

