

## Tap wrench Basic

For holding square-head screw taps and reamers in accordance with DIN 10

**ORION**<sup>®</sup>

### Application:

For holding square-head screw taps in accordance with DIN 10, reamers, screw extractors, screw tap extensions, tools with square mounts

### Version:

- Housing, size 0-5, made of die-cast zinc, zinc-plated arm with knurling for medium loads

### Advantage:

- Die-cast zinc ensures excellent value for money
- Ground and hardened steel jaws



|  |                  |
|--|------------------|
| <b>Art. no.</b>                                  | <b>13549 030</b> |
| <b>Tap wrench size</b>                           | 3                |
| <b>Suitable for min./max. square socket size</b> | 4.9-12 mm        |
| <b>Min./max. reamer cutting range</b>            | 7-15 mm          |
| <b>Min./max. thread-cutting area, metric</b>     | 5-20 mm          |
| <b>Length</b>                                    | 370 mm           |

### EAN-Code

4039247076673