

Thread milling cutter solid carbide TiAlN 2xD straight shank HA

For universal use up to 1500 N/mm² in female threads

ORION[®]

Application:

For producing metric right-hand and left-hand threads on CNC machines in through holes and blind holes in the steel, stainless steel, non-ferrous metals, cast iron and special alloy material groups up to a strength of 1500 N/mm².



Execution:

- Thread milling cutters with short thread section

Art. no.	13496 088
Brand	ORION
Manufacturer Part Number	13496088
Cutting material	SC
Surface	TiAlN
Hole type	Clearance/blind hole ≤ 2xD
Tool holding device	HA parallel shank
Cutting edge diameter	3.1 mm
Pitch	0.7 mm
Suitable for metric threads from	M4
Length	58 mm
Effective length of thread milling	9 mm
Shank diameter	6 mm
Number of cutting edges	3 PCS
f steel 1000	0.05 mm/r
Gross Weight	0.023 kg
Product Group	1DD

EAN

405362539789 1