

September 27, 2019

Products

New compact form factors for DC link applications

The portfolio of EPCOS film capacitors for DC link applications has been extended with the new B3277*X/Y/Z series. The new capacitors feature compact dimensions, high capacitance density and high current capability. They are designed for rated voltages of between 500 V DC and 1200 V DC. The series offers numerous standard capacitance values within the range from 1.5 μ F to 170 μ F. Depending on the voltage and capacitance, their lead spacings are 27.5 mm, 37.5 mm and 52.5 mm, with both 4-pin or 2-pin versions available for each lead spacing. The maximum operating temperature of these RoHS-compatible components is 105 °C. At a rated voltage and an operating temperature of 85 °C the typical service life of the self-healing capacitors is 60,000 hours.

The MKP capacitors are suitable for use in DC link circuits, as DC filters and for power factor correction for industrial converters, as well as for power supplies with higher reliability requirements. These applications include X-ray equipment, LED street lighting, induction hobs and electrical chargers.

You can find further information on the products at

www.tdk-electronics.tdk.com/en/film_mkp

Contact Sladana Matijevic, CAP PM FILM DC, Munich

Customers are asked to address inquiries directly to their sales contacts.

TDK Electronics AG

Rosenheimer Strasse 141 e, 81671 Munich · Post: P.O.Box 80 17 09, 81617 Munich, Germany
Headquarters: Munich · Commercial register of the local court (Amtsgericht): Munich HRB 127250
Chairman of the Supervisory Board: Dr. Werner Faber
Management Board: Joachim Zichlarz, Chairman · Joachim Thiele · Dr. Werner Lohwasser
www.tdk-electronics.tdk.com

Film Capacitors

Internal / External

190927FILM1e