

LOCTITE[®] SI 5366™

Known as LOCTITE[®] 5366™ May 2014

PRODUCT DESCRIPTION

LOCTITE[®] SI 5366[™] provides the following product characteristics:

Technology	Silicone		
Chemical Type	Acetoxy silicone		
Appearance (uncured)	Clear paste		
Components	One component -		
	requires no mixing		
Cure	Room temperature vulcanizing (RTV)		
Application	Bonding or Sealing		
Flexibility	Enhances load bearing & shock absorbing characteristics of the bond area.		

LOCTITE[®] SI 5366™ has been designed specifically for use as a bonding agent to ensure perfect sealing, as well as bonding and protection. Typical applications include sealing side windows in trains, sealing heat sources (ovens, heat exchangers, steam circuits, water heaters), providing protection/insulation of electrical boxes, bonding of HCR silicones and in the general care and maintenance applications in various fields. This product is typically used in applications up to 250 °C.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Specific Gravity @ 25 °C	1.04
Extrusion Rate, g/min	100
Flow, ISO 7390, mm	<2

Flash Point - See SDS


TYPICAL CURING PERFORMANCE

Surface Cure

LOCTITE[®] SI 5366[™] becomes tack free on exposure to atmospheric moisture within 5 minutes at 23±2°C / 50±5%RH.

Depth of Cure

The graph below shows the increase in depth of cure with time at 23 ± 2 °C / 50 ± 5 % RH.



TYPICAL PROPERTIES OF CURED MATERIAL

After 7days @ 25 °C / 50% RH, 0.5 mm thick film

Physical Properties:

Shore Hardness, ISO 868, Durometer A		25
Elongation, at break, ISO 37, %		530
Tensile Strength, ISO 37	N/mm² (psi)	2.5 (360)
	(psi)	(300)

Electrical Properties:

Dielectric Breakdown Strength,	18
IEC 60243-1, kV/mm	
Volume Resistivity, IEC 60093, Ω·cm	1×10 ¹
Dielectric Constant, IEC 60250:	
1MHz	2.8

TYPICAL PERFORMANCE OF CURED MATERIAL Adhesive Properties

Cured for 7 days @ 25 °C / 50% RH Lap Shear Strength, ISO 4587:

•	0 /				
Aluminum(1	mm	sand-blasted	thick	N/mm²	2
bondline)				(psi)	(290)

TYPICAL ENVIRONMENTAL RESISTANCE

Typical Fluid Immersion Properties

Aged @ 22 °C for 5,000 hours, 2 mm thick film:

Sodium Carbonate, 25%:

Volume Swell, %	-0.2
Change in Tensile Strength, %	-12
Change in Elongation, %	-10



Sodium Chloride, 25%: Volume Swell, % Change in Tensile Strength, %	-0.1 0
Change in Elongation, % Hydrochloric Acid, 2%:	0
Volume Swell, % Change in Tensile Strength, % Change in Elongation, %	-0.1 -8 -8
Lactic Acid, 12%: Volume Swell, % Change in Tensile Strength, % Change in Elongation, %	0.3 4 10
Citric Acid, 12%: Volume Swell, % Change in Tensile Strength, % Change in Elongation, %	-0.1 -0.3 0
Soda, 25%: Volume Swell, % Change in Tensile Strength, % Change in Elongation, %	-7 -15 -15
Bleach, commercial concentration: Volume Swell, % Change in Tensile Strength, % Change in Elongation, %	-1 -20 -15

GENERAL INFORMATION

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

For safe handling information on this product, consult the Safety Data Sheet (SDS).

Directions for use:

- For best performance bond surfaces should be clean and free from grease.
- Moisture curing begins immediately after the product is exposed to the atmosphere, therefore parts to be assembled should be mated within a few minutes after the product is dispensed.
- 3. When joint is assembled pressure should be applied to spread the adhesive out and fill the joint completely.
- The bond should be allowed to cure (e.g. seven days), before subjecting to heavy service loads.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: 8 °C to 21 °C. Storage below 8 °C or greater than 28 °C can adversely affect product properties. Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

 $(^{\circ}C \times 1.8) + 32 = ^{\circ}F$ kV/mm x 25.4 = V/mil mm / 25.4 = inches μ m / 25.4 = mil N x 0.225 = lb N/mm x 5.71 = lb/in N/mm² x 145 = psi MPa x 145 = psi M·m x 8.851 = lb·in N·m x 0.738 = lb·ft N·mm x 0.142 = oz·in mPa·s = cP

Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits. The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. [®] denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 1.2