

SCLC HSS boring bar, positive left

for face and longitudinal turning using CC indexable insert

ATORN[®]

Application

For copy turning and longitudinal turning using CC indexable insert 80°.

Version

- precision-manufactured **HSS** boring bar, with inner cooling, C type, 95° pitch angle, 80° tip angle, 7° clearance angle

Advantage

- universal use for facing and longitudinal turning
- positive body geometry ensures low cutting forces
- very high rigidity and excellent cutting quality thanks to HSS supporting material



Art. No.	17846 355
ISO name	AH 16 Q SCLC R/L 09
Min. bore diameter	18 mm
Shaft diameter	16 mm
Cutting edge height	7.5 mm
Clearance length	27 mm
Length	180 mm
Clamping surface height	15 mm
Programming size	9 mm
Suitable for indexable inserts	CC.. 09T3..
Tool design	Left
DIN	8024

EAN-Code

4050293320343