

Thread milling cutter solid carbide TiAlN 3xD straight shank HA

For universal use up to 1500 N/mm² in female threads

ORION[®]

Execution:

- Thread milling cutters with short thread section

Advantage:

- Innovative cutting geometry for very high dimensional accuracy, process reliability and chip removal.
- Thread milling cutting of very small threads from M1.4 x 0.3 possible



Art. no.	13496 096
Brand	ORION
Manufacturer Part Number	13496096
Cutting material	SC
Surface	TiAlN
Hole type	Clearance/blind hole ≤ 3xD
Tool holding device	HA parallel shank
Cutting edge diameter	2.75 mm
Pitch	0.6 mm
Suitable for metric threads from	M3.5
Length	58 mm
Effective length of thread milling	10.5 mm
Shank diameter	6 mm
Number of cutting edges	3 PCS
f steel 1000	0.05 mm/r
Gross Weight	0.024 kg
Product Group	1DD

EAN

4053625397976