

Product characteristics

Inductive sensor

Metal thread M30 x 1.5

Cable

Sensing range 10 mm; [f] flush mountable

Electrical data

Electrical design

DC PNP

Operating voltage [V]

10...36 DC

Current consumption [mA]

15 (24 V)

Protection class

II

Reverse polarity protection

yes

Outputs

Output function

complementary

Voltage drop [V]

< 2.5

Current rating [mA]

250

Short-circuit protection

pulsed

Overload protection

yes

Switching frequency [Hz]

400

Range

Sensing range [mm]

10

Real sensing range (Sr) [mm]

10 ± 10 %

Operating distance [mm]

0...8.1

Accuracy / deviations

Correction factors

mild steel = 1 / stainless steel approx. 0.7 / brass approx. 0.5 / Al approx. 0.4 / Cu approx. 0.3

Hysteresis [% of Sr]

3...15

Switch-point drift [% of Sr]

-10...10

Environment

Ambient temperature [°C]

-25...80

Protection

IP 67

Tests / approvals

EMC

EN 60947-5-2

EN 55011:

class B

MTTF [Years]

1365

Mechanical data

Mounting

flush mountable

Housing materials

Brass nickel-plated; PBT (Pocan)

Weight [kg]


0.231

Displays / operating elements

Output status indication LED

yellow

II5162 - Inductive sensor - eclass: 27270101 / 27-27-01-01

Electrical connection	
Connection	PVC cable / 2 m; 4 x 0.34 mm²
Wiring	
Core colours	
BK	black
BN	brown
BU	blue
WH	white
	
Accessories	
Accessories (included)	2 lock nuts
Remarks	
Pack quantity	[piece] 1
ifm electronic gmbh • Friedrichstraße 1 • 45128 Essen — We reserve the right to make technical alterations without prior notice. — GB — II5162 — 06.03.2003	