

Thread cutting tool set M3 to M24 HSS through hole/blind hole ≤ 1xD

For universal use up to 1000 N/mm²

ORION[®]

Application:

for producing **metric (M)** male and female threads by hand in blind holes and through holes, in steel, non-ferrous metals and (cast-iron) material groups up to a strength of 1000 N/mm².

Execution:

- Hand tap sets, HSS, comprising taper tap with one ring (Type A), second tap with two rings (Type D) and third tap (plug) (Type C) and die with tap wrench, die holder and thread gauge

Advantage:

- Standard geometry with very good price/performance ratio



Art. no.	13399 900
Brand	ORION
Manufacturer Part Number	13399900
Thread type	Metric thread
Hole type	Clearance/blind hole ≤ 1xD
Cutting material	HSS
Composition of set	3 hand taps for each size (taper tap/second tap/third tap (plug)) and 1 die for each size M3/M4/M5/M6/M8/M10/M12/M14/M16/M18/M20/M22/M24
Gross Weight	11.000 kg
Product Group	1DC

EAN

4053625270699