

Test stand, model 103

For tensile and compressive force measuring units

—
Test

Application:

For reliable acquisition of forces and paths, torques and angles required when inspecting materials and assemblies. Potential areas of application are, for example, incoming/outgoing goods inspection and occasional quality checks in production.

Execution:

- Electronically-operated tensile/compression test frames
- Primarily for tensile and compressive forces up to 1000 N
- When combined with a force measuring unit, this test frame forms a complete inspection machine
- Integrated incremental travel measurement
- Automatic switch-off when limit values are reached
- Centrally-arranged drive spindle

Advantage:

- Easy to use
- High stability
- Cost-effective and high-quality solution for small-scale inspections



Art. no.	42455 030
Brand	TEST
Manufacturer Part Number	P103.1KN
Max. force range	1000 N
Travel motion	Motorised
Overall stroke	550 mm
Gross Weight	22.000 kg
Product Group	443