

## Conical washers DIN 6319 type G



### Application:

For transferring clamping forces in cases where clamping elements need to adapt to uneven clamping surfaces.

### Execution:

- Stamped, pressed and tempered

### Advantage:

- Thanks to the large diameter, these are particularly ideal for clamping via the slot in the case of clamps.



|   |                  |
|---|------------------|
| <b>Art. no.</b>                           | <b>26208 716</b> |
| <b>Brand</b>                              | AMF              |
| <b>Manufacturer Part Number</b>           | 82008            |
| <b>Suitable cheese-head screw DIN 912</b> | M12              |
| <b>Internal diameter</b>                  | 14.2 mm          |
| <b>Outer diameter</b>                     | 36 mm            |
| <b>Height</b>                             | 6 mm             |
| <b>Diameter</b>                           | 20 mm            |
| <b>DIN</b>                                | 6319             |
| <b>Gross Weight</b>                       | 0.039 kg         |
| <b>Product Group</b>                      | 260              |

### EAN

4020772082000