



MTA | SL-156


TE Internal #: 640706-2

SL-156, Connector Contact, Socket, Wire-to-Wire / Wire-to-Board,
24 – 18AWG Wire Size, .2 – .9mm² Wire Size, Pre-Tin, Bag/Box,
Wire & Cable

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Contacts >

Wire-to-Board Connector Contacts: socket, wire size 30-16 AWG, SL 156



Contact Type: **Socket**
Connector System: **Wire-to-Board, Wire-to-Wire**
Wire Size: **.2 – .9 mm²**
Contact Mating Area Plating Material: **Pre-Tin**

[All Wire-to-Board Connector Contacts: socket, wire size 30-16 AWG, SL 156 \(24\)](#)

Features

Product Type Features

Applied Pressure	High
Connector System	Wire-to-Board, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Mating Square Post Dimension	1.14 mm[.045 in]
Contact Retention Within Housing	With
Wire Contact Termination Area Plating Material Thickness	.33 μm



Wire Contact Termination Area Plating Material	Pre-Tin
Contact Mating Area Plating Material Thickness	3.302 μm[130 μin]
Contact Base Material	Brass
Contact Type	Socket
Contact Mating Area Plating Material	Pre-Tin
Contact Current Rating (Max)	6.5 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
Connector Mounting Type	Cable Mount (Free-Hanging)

Dimensions

Accepts Wire Insulation Diameter Range	2.8 mm[.11 in]
Wire Size	.2 – .9 mm ²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag/Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 58614-1
PROCRIMP, HT&D SL156

TE Part # 58614-2
PROCRIMP, DIE, SL156

TE Part # 90471-1
EXTRACTION TOOL, SC-156

TE Part # 91597-1
CCII SL-156 REC 24-18 ASSY

TE Part # 91597-3
CCII SL-156 REC 24-18 HEAD

Also in the Series | SL-156

Insertion & Extraction Tools(1)

PCB Connector Keying(2)

PCB Latches, Locks & Retainers(1)

Rectangular Connector Housings(12)



Rectangular Connector Keying Plugs(1)



Wire-to-Board Connector Assemblies & Housings(157)



Wire-to-Board Connector Contacts(24)

Customers Also Bought



TE Part #1658642-1
D-Sub Crimp: Plug, Signal, 9 Posn, Pin Size 20, Shell Size 1



TE Part #1658622-3
16 NOVO MIL/CTR 30DP,LEAD FREE



TE Part #1-770988-0
MINI UMNL SOK 22-18AWG AU



TE Part #1658622-2
14 NOVO MIL/CTR 30DP,LEAD FREE



TE Part #1-770186-1
12P MINI UMNL ASSY VO SNAU LF




TE Part #170325-5
187 PL MKII REC. 20-16AWG PTBR



TE Part #2-520080-2
ULTRA-FAST .110/.125 ASY REC 22-18 TPBR



TE Part #102153-8
AMP-LATCH UNIVERSAL HEADERS



TE Part #173725-1
PL 187 REC TERMINAL 20-14 PTPB LP



TE Part #A039813001
VG-95218-T028-D002CK3100

Documents

Product Drawings

CONTACT .045 POST PT BRASS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_640706-2_G.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_640706-2_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_640706-2_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[MTA, CST-100 II, SL-156 and AMP Economy Power \(EP\) Connectors](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English