

## TEGERA® 8800 INFINITY

Synthetic glove, nitrile, palm-dipped, nylon, spandex, 15 gg, smooth finish, Cat. II, black, yellow, withstands contact heat up to 100°C, oil and grease resistant palm, for precision work

### PROPERTIES

High level of protection, extremely good fingertip sensitivity, extra flexible, good grip, extra comfortable, extremely light

### SPECIFICATION

TYPE OF GLOVE Work gloves - General handling

CATEGORY Cat. II

SIZE RANGE (EU) 5, 6, 7, 8, 9, 10, 11

COLLECTION Infinity

LINER MATERIAL Nylon, spandex, 15 gg

DIPPING Palm-dipped

DIPPING MATERIAL Nitrile

DEXTERITY 5

GRIP PATTERN Smooth finish

CUFF STYLE Knitwrist cuff

COLOUR Black, yellow

PAIRS PER PACKAGE/CARTON 6/120

DISPLAY Hook

MATERIAL SPECIFICATION Nitrile, nylon, elastane



I N F I N I T Y™



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

## TEGERA® 8800 INFINITY

### FEATURES

Withstands contact heat up to 100°C, approved for handling foodstuffs, anatomically designed

### PREVENTS RISK OF

Abrasion injuries, blisters, grazes, scratches, lacerations, contact with dirt, drying out, chapping, contact with oil and fat

### PRIMARY ENVIRONMENTS OF USE

Dry environments, moist environments, dirty environments

### PRIMARY AREAS OF USE

Fine assembly, machine operating, installation work, HVAC installation, engineering, transport work, machine driving, warehouse work, airport work, repair work, service work, shop work

### PRIMARY INDUSTRIES OF USE


Machinery and equipment, MRO, automotive, transportation, utilities, building and construction, logistics, facilities, service, retail

### TYPE OF WORK

Light weight



CE Cat. II



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2018-05-14

2(3)

**ejendals**  
PROTECTING HANDS AND FEET

**EJENDALS AB**

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com

# TEGERA® 8800 INFINITY

## EC TYPE EXAMINATION

Notified Body: 0075 CTC, 4 rue Hermann Frenkel, 69367 Lyon Cedex 07 France

## COMPLIANCE DESCRIPTION

EN 420:2003 + A1:2009 Protective gloves - general requirements and test methods

EN 388:2003 Protective gloves against mechanical risks

Property	Level Achieved	(Maximum Performance)
A) Resistance to abrasion (No. of revolutions)	4	(4)
B) Resistance to cutting (Index)	1	(5)
C) Tear resistance (Newton)	2	(4)
D) Puncturing resistance (Newton)	1	(4)

EN 388 - Testing (specifies the requirements that apply for each safety level).


Level of protection/Performance level	1	2	3	4	5
A) Resistance to abrasion (No. of revolutions)	100	500	2 000	8 000	
B) Resistance to cutting (Index)	1,2	2,5	5,0	10,0	20,0
C) Tear resistance (Newton)	10	25	50	75	
D) Puncturing resistance (Newton)	20	60	100	150	


EN 407:2004 Protective gloves against thermal risks (heat and/or fire)


CONFIDENCE IN TEXTILES Tested for harmful substances according to Oeko-Tex® Standard 100



CE Cat. II

 EN 388:2003 4121

 EN 388:2016 4121X

 EN 407:2004 X1XXXX



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2018-05-14

**ejendals**  
PROTECTING HANDS AND FEET

**EJENDALS AB**

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com