



SAFETY DATA SHEET
Strong Toilet Cleaner Swan Neck

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name Strong Toilet Cleaner Swan Neck

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Cleaning agent.

1.3. Details of the supplier of the safety data sheet

Supplier CROWN SUPPLIES LTD
UNIT 3,
VULCAN ROAD NORTH
NORWICH, NORFOLK
NR6 6AQ
T. 01603 403333
sales@crownsupplies.co.uk

1.4. Emergency telephone number

Emergency telephone Emergency contact number 01295 251721 (9am to 5pm Monday to Friday excluding bank holidays). Ask for Technical Department quoting the product name. Outside of these hours please contact your doctor or local hospital accident and emergency department or the NHS enquiry service (dial 111) quoting product name and present this MSDS advising them that the product is registered with the National Poisons Information Service

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards Not Classified

Health hazards Skin Irrit. 2 - H315 Eye Dam. 1 - H318 STOT SE 3 - H335 Aquatic

Environmental hazards Acute 1 - H400 Aquatic Chronic 3 - H412

Classification (67/548/EEC or 1999/45/EC) Xi;R36/37/38.

2.2. Label elements Pictogram



Signal word

Danger

Strong Toilet Cleaner Swan Neck

Hazard statements	H315 Causes skin irritation. H318 Causes serious eye damage. H335 May cause respiratory irritation. H400 Very toxic to aquatic life. H412 Harmful to aquatic life with long lasting effects.
Precautionary statements	P261 Avoid breathing vapour/ spray. P264 Wash contaminated skin thoroughly after handling. P273 Avoid release to the environment. P280 Wear protective gloves. P280 Wear eye protection. P302+P352 IF ON SKIN: Wash with plenty of water. P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing. P305 +P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P310 Immediately call a POISON CENTER/ doctor. P332+P313 If skin irritation occurs: Get medical advice/ attention. P391 Collect spillage. P501 Dispose of contents/ container in accordance with national regulations.
Contains	HYDROCHLORIC ACID ...%, BIS (2-HYDROXYETHYL) OLEYL AMINE
Supplementary precautionary statements	P321 Specific treatment (see medical advice on this label). P342+P311 If experiencing respiratory symptoms: Call a POISON CENTER/ doctor. P362+P364 Take off contaminated clothing and wash it before reuse.

2.3. Other hazards

Other Hazards None

SECTION 3: Composition/information on ingredients

3.2. Mixtures

HYDROCHLORIC ACID ...%CAS	10-30%
number: 7647-01-0	EC number: 231-595-7
Classification Skin Corr. 1B - H314 Eye Dam. 1 - H318 STOT SE 3 - H335	Classification (67/548/EEC or 1999/45/EC) C;R34 Xi;R37
BIS (2-HYDROXYETHYL) OLEYL AMINE CAS	1-5%
number: 25307-17-9	EC number: 246-807-3
M factor (Acute) = 10	
Classification Acute Tox. 4 - H302 Skin Corr. 1B - H314 Eye Dam. 1 - H318 Aquatic Acute 1 - H400	Classification (67/548/EEC or 1999/45/EC) Xn;R22. C;R34. N;R50.

Strong Toilet Cleaner Swan Neck

BENZALKONIUM CHLORIDE CAS	<1%
number: 68424-85-1 M factor (Acute) = 10	M factor (Chronic) = 1
Classification Met. Corr. 1 - H290 Acute Tox. 4 - H312 Skin Corr. 1B - H314 Eye Dam. 1 - H318 Aquatic Acute 1 - H400 Aquatic Chronic 1 - H410	Classification (67/548/EEC or 1999/45/EC) Xn;R21/22. C;R34. N;R50.
PHOSPHORIC ACID ...%CAS	<1%
number: 7664-38-2	EC number: 231-633-2
	REACH registration number: 01-2119485924-24-XXXX
Classification Skin Corr. 1B - H314 Eye Dam. 1 - H318	Classification (67/548/EEC or 1999/45/EC) C;R34

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation	Move affected person to fresh air at once. Rinse nose and mouth with water. Get medical attention if any discomfort continues.
Ingestion	Never give anything by mouth to an unconscious person. Do not induce vomiting. Rinse mouth thoroughly with water. Get medical attention if any discomfort continues.
Skin contact	Remove affected person from source of contamination. Remove contaminated clothing. Wash skin thoroughly with soap and water. Get medical attention if irritation persists after washing.
Eye contact	Remove affected person from source of contamination. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes and get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation	May cause respiratory irritation. May
Ingestion Skin	cause discomfort if swallowed. May
contact Eye	cause skin irritation.
contact	May cause eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Specific treatments	Seek medical attention if irritation or symptoms persist. Symptomatic treatment
----------------------------	---

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	The product is not flammable. Use fire-extinguishing media suitable for the surrounding fire.
-------------------------------------	---

5.2. Special hazards arising from the substance or mixture

Strong Toilet Cleaner Swan Neck

Specific hazards Burning may produce irritating, toxic and obnoxious fumes.
Oxides of Carbon, Nitrogen and Sulphur.

5.3. Advice for firefighters

Special protective equipment for firefighters Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Wear protective clothing as described in Section 8 of this safety data sheet.

6.2. Environmental precautions

Environmental precautions Avoid or minimise the creation of any environmental contamination.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Stop leak if possible without risk. Absorb in vermiculite, dry sand or earth and place into containers. Flush contaminated area with plenty of water. Avoid the spillage or runoff entering drains, sewers or watercourses.

6.4. Reference to other sections

Reference to other sections See section 3,8 & 13 for further information

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Avoid spilling. Avoid contact with skin and eyes.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Store in tightly-closed, original container in a dry, cool and well-ventilated place. Keep only in the original container.

Storage class Chemical storage.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SHELF LIFE OF DILUTION 12 MONTHS

SECTION 8: Exposure Controls/personal protection

8.1. Control parameters

Occupational exposure limits

PHOSPHORIC ACID ...%

Long-term exposure limit (8-hour TWA): WEL 1 mg/m³

Short-term exposure limit (15-minute): WEL 2 mg/m³ WEL

= Workplace Exposure Limit

Ingredient comments WEL = Workplace Exposure Limits

8.2. Exposure controls

Protective equipment



Strong Toilet Cleaner Swan Neck

Appropriate engineering controls	Provide adequate ventilation. Avoid inhalation of vapours. Observe any occupational exposure limits for the product or ingredients.
Eye/face protection	Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Personal protective equipment for eye and face protection should comply with European Standard EN166. The following protection should be worn: Chemical splash goggles or face shield.
Hand protection	Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. To protect hands from chemicals, gloves should comply with European Standard EN374.
Other skin and body protection	Wear appropriate clothing to prevent any possibility of skin contact.
Hygiene measures	Do not smoke in work area. Wash at the end of each work shift and before eating, smoking and using the toilet. Wash promptly if skin becomes contaminated. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.
Respiratory protection	No specific recommendations. Respiratory protection may be required if excessive airborne contamination occurs.

SECTION 9: Physical and Chemical Properties

9.1. Information on basic physical and chemical properties

Appearance	Liquid.
Colour Odour	Blue.
pH	Pungent. pH (concentrated solution): <2
Initial boiling point and range	100°C @ 760 mm Hg
Relative density	1.09 @ 20°C

9.2. Other information

Other information	None.
--------------------------	-------

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity	No test data specifically related to reactivity available for this product or its ingredients.
-------------------	--

10.2. Chemical stability

Stability	Stable at normal ambient temperatures.
------------------	--

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	None known.
---	-------------

10.4. Conditions to avoid

Conditions to avoid	Avoid excessive heat for prolonged periods of time.
----------------------------	---

10.5. Incompatible materials

Materials to avoid	None known.
---------------------------	-------------

10.6. Hazardous decomposition products

Strong Toilet Cleaner Swan Neck

Hazardous decomposition products Fire creates: Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral

ATE oral (mg/kg) 18,518.52

Inhalation Irritating to respiratory system. May

Ingestion cause discomfort if swallowed.

Skin contact Irritating to skin.

Eye contact Irritating to eyes.

SECTION 12: Ecological Information

Ecotoxicity Not regarded as dangerous for the environment.

12.1. Toxicity

Toxicity The product is not believed to present a hazard due to its physical nature.

12.2. Persistence and degradability

Persistence and degradability The product is biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

12.4. Mobility in soil

Mobility The product is soluble in water.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This product does not contain any substances classified as PBT or vPvB.

12.6. Other adverse effects

Other adverse effects None known.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Disposal methods Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

SECTION 14: Transport information

General The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

Strong Toilet Cleaner Swan Neck

14.3. Transport hazard class(es)

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations	The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (SI 2009 No. 716).
Guidance	Workplace Exposure Limits EH40. CHIP for everyone HSG228. Approved Classification and Labelling Guide (Sixth edition) L131. Safety Data Sheets for Substances and Preparations

15.2. Chemical safety assessment

A chemical safety assessment has been carried out.

SECTION 16: Other information

Revision date	03/07/2017
Revision	7
Supersedes date	27/01/2016
SDS number Risk	PLF418
phrases in full	R21/22 Harmful in contact with skin and if swallowed. R22 Harmful if swallowed. R34 Causes burns. R36/37/38 Irritating to eyes, respiratory system and skin. R37 Irritating to respiratory system. R50 Very toxic to aquatic organisms.

Strong Toilet Cleaner Swan Neck

Hazard statements in full

H290 May be corrosive to metals.
H302 Harmful if swallowed.
H312 Harmful in contact with skin.
H314 Causes severe skin burns and eye damage. H315 Causes skin irritation.
H318 Causes serious eye damage.
H335 May cause respiratory irritation.
H400 Very toxic to aquatic life.
H410 Very toxic to aquatic life with long lasting effects.
H412 Harmful to aquatic life with long lasting effects.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.