

## Mico Pro Power module

IN: 24 V DC / 40A, 16mm<sup>2</sup> / Cover plate included

Mico Pro® PM 24 V DC/40 A

Cover plate included

Shock load


1/2 sin 30 g, 11 ms

Build your own Mico Pro® online:

[START](#)

## Link to Product

### Illustration



Product may differ from Image



### Commercial data

ECLASS-6.0	27371802
ECLASS-6.1	27371890
ECLASS-7.0	27371890

ECLASS-8.0	27371802
ECLASS-9.0	27371802
ECLASS-10.1	27371802
ECLASS-11.1	27371802
ECLASS-12.0	27371802
ETIM-5.0	EC001440
customs tariff number	85363030
GTIN	4048879830454
Packaging unit	1

**Electrical data | Supply**

Total current max.	40 A
--------------------	------

**Electrical data | Input**

CTRL input voltage control inputs high min.	9 V
CTRL input voltage control inputs high max.	30 V
CTRL signal	ON/OFF
Input voltage 1 DC	12 V
Input voltage 2 DC	24 V
Input voltage DC min.	9 V
Input voltage DC max.	30 V
ON input voltage control inputs min.	9 V
ON input voltage control inputs max.	30 V
ON pulse length control inputs high min.	120 ms
Total current bridge set max.	40 A

**Electrical data | Output**

Switching voltage AC max.	30 V
Switching voltage DC max.	30 V

**Installation**

Connection cross-section static min.	0,75 mm <sup>2</sup>
Connection cross section static max.	16 mm <sup>2</sup>
Connection cross-section dynamic min.	0,75 mm <sup>2</sup>
Connection cross section dynamic max.	16 mm <sup>2</sup>
AWG number static min.	4
AWG number static max.	20
AWG number dynamic min.	4
AWG number dynamic max.	20

**Installation | Connection**

Connection	Bridge system
------------	---------------

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

**Device protection | Mechanical**

Shock resistance (EN IEC 60068-2-27)	30 g, 11 ms 1/2 sin
--------------------------------------	---------------------

**Mechanical data | Mounting data**

Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Height	130 mm
Width	24 mm
Depth	114 mm

**Environmental characteristics | Climatic**

Operating temperature min.	-25 °C
Operating temperature max.	55 °C

Storage temperature min.	-40 °C
Storage temperature max.	80 °C

**Connection type 10**

Family construction form	Bridging Contact
Gender	female
Color contact carrier	black
No. of poles	1
PIN 1	UB In + 24 V DC
Family construction form	Bridging Contact
Gender	female
Color contact carrier	black
No. of poles	1
PIN 1	0 V
Family construction form	Bridging Contact
Gender	female
Color contact carrier	black
No. of poles	4
PIN 1	On
PIN 2	Ctrl
PIN 3	Alarm
PIN 4	0.9
Family construction form	Bridging Contact
Gender	male
Color contact carrier	black
No. of poles	4
PIN 1	On
PIN 2	Ctrl
PIN 3	Alarm
PIN 4	0.9
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	4
PIN 1	Alarm 1
PIN 2	Alarm 2
PIN 3	Alarm 3
PIN 4	Alarm 4
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	4
PIN 1	Out 1
PIN 2	Out 2
PIN 3	Out 3
PIN 4	Out 4
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	4
PIN 1	0 V 1
PIN 2	1 V 2

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-05-14

PIN 3	2 V 3
PIN 4	3 V 4
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	4
PIN 1	90% 1
PIN 2	90% 2
PIN 3	90% 3
PIN 4	90% 4
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	4
PIN 1	On 1
PIN 2	On 2
PIN 3	On 3
PIN 4	On 4
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	4
PIN 1	Ctrl 1
PIN 2	Ctrl 2
PIN 3	Ctrl 3
PIN 4	Ctrl 4