6W Isolated DC to DC Converters - Dual Output

multicomp PRO

6W isolated DC-DC converter in SIP package Wide input and regulated dual output





CE Patent Protection

Features

- · Wide 4:1 input voltage range
- High efficiency up to 83%
- No-load power consumption as low as 0.12W
- I/O isolation test voltage 1.5K VDC
- · Input under-voltage protection, output short circuit, over-current protection
- Operating ambient temperature range: -40°C to +85°C
- · Industry standard pin-out
- · EN62368 approved

These series of isolated 6W DC-DC products with a 4:1 input voltage range. They feature efficiencies of up to 83%, 1500VDC input to output isolation, operating ambient temperature range of -40°C to +85°C, input under-voltage protection, output over-current, short circuit protection and they are widely used in applications such as medical care, industrial control, electric power, instruments and communication fields.

Selection Guide							
	Input Voltage (VDC)		Output		Full Load Efficiency	Conscitive Lond(v.E)*	
Part Number	Nominal (Range)	Max.	Voltage (VDC)	Current (mA) Max./Min.	Full Load Efficiency (%) Min./Typ.	Capacitive Load(μF)* Max.	
MPRA2405S-6W	24 (9 to 36)		±5	±600	78/80	470	
MPRA2412S-6W		40	±12	±250	81/83	120	
MPRA2415S-6W		40	±15	±200	81/83	100	
MPRA2424S-6W			±24	±125	80/82	68	

Notes: 1 Exceeding the maximum input voltage may cause permanent damage;

³ The specified maximum capacitive load for positive and negative output is identical.

Input Specifications					
Item	Operating Conditions	Min.	Тур.	Max.	Unit
	±5V output	-	312/12	320/16	
Input Current (full load / no- load)	±9V/±12V/±15V output	-	301/12	309/16	
loddy	±24V output	-	305/12	313/16	mA
Reflected Ripple Current		-	50	-	
Surge Voltage(1sec. max.)		-0.7	-	50	
Start-up Voltage		-	-	9	V DC
Input Under-voltage Protection		5.5	6.5	-	
Input Filter		Capacitance filter			
Hot Plug			Unavailal	ole	
	Module on	Ctrl pin open or pulled high (3.5-12VDC)			2VDC)
Ctrl*	Module off	Ctrl pin pulled low to GND (0-1.2VDC)			VDC)
	Input current when off		6	10	mA
Note: * Refer to DC-DC Converter Application Notes for detailed description of reflected ripple current test method.					

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



² Efficiency is measured at nominal input voltage and rated output load;

6W Isolated DC to DC Converters - Dual Output



Output Specifications

Item	Operating Conditions		Min.	Тур.	Max.	Unit
Voltage Assurage	F0/ 1000/ load	Vo1		±1.5	±2	%
Voltage Accuracy	5% -100% load	Vo2]	±2	±3	
Linear Description	Input voltage variation	Vo1]	±0.5	±1	
Linear Regulation	from low to high at full load	Vo2]	±1	±1.5	
Load Decidation	F0/ 4000/ load	Vo1		±0.8	±1.5	%
Load Regulation	5% -100% load	Vo2		±1.2	±2	
Cross Regulation	25% load step change, nominal input voltage			-	±5]
Transient Recovery Time				450	500	μs
Transient Beauches Deviation	25% load step change,	±5V output	_	±5	±8	. %
Transient Response Deviation	nominal input voltage	Others		±3	±5	
Temperature Coefficient Full load		1	-	±0.03	%/°C	
Ripple & Noise* 20MHz bandwidth, 5% -100% load]	120	150	mVp-p	
Over-current Protection Input voltage range			110	160	230	%lo
Short-Circuit Protection	Input voltage range		Continuous, self-recovery			

Note: 1. At 0%~5% load, the Vo1 Max. output voltage accuracy is ±3%, the Vo2 Max. output voltage accuracy is ±5%.

Application Notes for specific information.

General Specifications						
Item	Operating Conditions	Min.	Тур.	Max.	Unit	
Isolation	Input-output electric strength test for 1 minute with a leakage current of 1mA max.	1500	-	-	VDC	
Insulation Resistance	Input-output insulation at 500VDC	1000	-	-	ΜΩ	
Isolation Capacitance	Input-output capacitance at 100KHz/0.1V	-	20	-	pF	
Operating Temperature	See Fig. 1	-40	-	105		
Storage Humidity	Without condensation	5	-	125		
Storage Temperature		-55	25	-	°C	
Pin Soldering Resistance Temperature	Soldering spot is 1.5mm away from case for 10 seconds	-	-	300		
Vibration		10-150Hz	z, 5G, 0.7	5mm. along	X, Y and Z	
Switching Frequency	PWM mode	-	500	-	kHz	
MTBF	MIL-HDBK-217F@25°C	1000	-	-	k hours	

Note:*Switching frequency is measured at full load. The module reduces the switching frequency for light load (below 50%) efficiency improvement.





^{2.} At 0%~100% load, the Vo1 regulation for 0%-100% load is ±4%, the Vo2 regulation for 0%-100% load is ±4.5%.

^{3.} Ripple & Noise at ≤ 5% load is no more than 180mV. The "parallel cable" method is used for Ripple and Noise test, please refer to DC-DC Converter

6W Isolated DC to DC Converters - Dual Output Multicomp PRO




Mechanical Specifications		
Case Material	Black plastic; flame-retardant and heat-resistant (UL94-V0)	
Dimensions	22 × 9.5 × 12 mm	
Weight	4.6g (Typ.)	
Cooling Method	Free air convection	

Electromagnetic Compatibility (EMC)

CE CE		CISPR32/EN55032 CLASS B (see Fig.3-2 for recommended circuit)	
Emissions RE CISPR32/EN55032 CLASS B (see Fig.3-2 for recommended circuit)			
	ESD	IEC/EN61000-4-2 Contact ±4KV	perf. Criteria B
	RS	IEC/EN61000-4-3 10V/m	perf. Criteria A
Immunity	EFT	IEC/EN61000-4-4 ±2KV (see Fig.3-1 for recommended circuit)	perf. Criteria B
	Surge	IEC/EN61000-4-5 line to line ±2KV (see Fig.3-1 for recommended circuit)	perf. Criteria B
	CS	IEC/EN61000-4-6 3 Vr.m.s	perf. Criteria A

Typical Characteristic Curves







Fig. 1

Design Reference

Typical application

All the DC/DC converters of this series are tested before delivery using the recommended circuit shown in Fig. 2. Input and/or output ripple can be further reduced by appropriately increasing the input & output capacitor values Cin and Cout and/or by selecting capacitors with a low ESR (equivalent series resistance). Also make sure that the capacitance is not exceeding the specified max. capacitive load value of the product.



Cin(µF)	Cout(µF)
100	22

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



6W Isolated DC to DC Converters - Dual Output multicomp

EMC compliance circuit





Fig. 3 Notes: For EMC tests we use Part ① in Fig. 3 for immunity and part ② for emissions test. Selecting based on needs

Components	Vin:24V
FUSE	Choose according to actual input current
C0, C4	330µF/100V
C1, C2, C3	10μF/50V
LDM1	10uH
LCM1	1.4-1.7mH (TN150P-RH12.7*12.7*7.9)
CY1, CY2	1nF/2KV

The products do not support parallel connection of their output


Dimensions and Recommended Layout



Note:

Unit: mm[inch]

Pin section tolerances: ±0.10[±0.004] General tolerances: $\pm 0.50[\pm 0.020]$



THIRD ANGLE PROJECTION

Note: Grid 2.54*2.54mm

Pin-Out				
Pin	Function			
1	GND			
2	Vin			
3	Ctrl			
5	NC			
6	+Vo			
7	0V			
8	-Vo			

26/02/21 V1.0

6W Isolated DC to DC Converters - Dual Output



Notes:

- 1. The maximum capacitive load offered were tested at input voltage range and full load;
- 2. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta=25°C, humidity<75%RH with nominal input voltage and rated output load;
- 3. All index testing methods in this datasheet are based on company corporate standards;
- 4. We can provide product customization service, please contact our technicians directly for specific information;
- 5. Products are related to laws and regulations: see "Features" and "EMC";
- Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

