

Micrometer

With cut-away frame

Mitutoyo

Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces
- Friction coupling for consistent, repeatable measuring force

Advantage:

- Insulated frame
- Cut-away frame (behind anvil) for measuring in hard-to-reach areas

Delivery:

Includes box, wrench, setting standard (from 25 mm), factory test certificate (0-50-mm measuring range)



Art. no.	32016 030
Brand	MITUTOYO
Manufacturer Part Number	102-311
Min./max. length measuring range	0-25 mm
Vernier scale	0.001 mm
Measuring surface diameter	6.3 mm
Measuring spindle increments	0.5 mm
Bracket depth	26 mm
Spindle clamping	Yes
Error limit	2 µm
Display	Nonius
Min./max. measurement force	5-10 N
Calibration Group	D
Gross Weight	0.280 kg
Product Group	3MA

EAN

4946368385822