

## INDIGA flat files

Type 9010

**LAPPORT**  
SCHLEIFTECHNIK

### Application:

For sharpening and reworking tools for wood, metal and plastic processing, e.g. scrapers, machine and plane knives, steels, reamers and gauges as well as measuring instruments.

### Execution:

- Best used with thin-bodied oil, petroleum or water
- Machined and wetted on all sides after burning

### Advantage:

- High endurance and grinding force



<b>Art. no.</b>	<b>69346 240</b>
<b>Brand</b>	LAPPORT
<b>Manufacturer Part Number</b>	100605
<b>Binding</b>	Ceramically bound
<b>Surface structure</b>	Medium
<b>Grid size</b>	150
<b>Form</b>	Flat
<b>Length</b>	150 mm
<b>Width</b>	16 mm
<b>Thickness</b>	8 mm
<b>Number of pieces per packet</b>	3 PCS
<b>Material of abrasive medium</b>	Corundum
<b>Suitable for finishing</b>	2 - suitable
<b>Suitable for main machining</b>	2 - suitable
<b>Suitable for surface inspection</b>	3 - less suitable
<b>Suitable for surface care</b>	2 - suitable
<b>Suitable for material rubber</b>	3 - less suitable
<b>Suitable for material cast iron</b>	2 - suitable
<b>Suitable for material HSS</b>	3 - less suitable
<b>Suitable for material carbide</b>	3 - less suitable
<b>Suitable for material ceramic</b>	3 - less suitable
<b>Suitable for material plastics</b>	3 - less suitable
<b>Suitable for material non-ferrous metals</b>	3 - less suitable
<b>Suitable for material steel (hardened)</b>	2 - suitable
<b>Suitable for material steel (unhardened)</b>	1 - very suitable
<b>Suitable for material tool steel</b>	2 - suitable
<b>ISO</b>	525
<b>Length x width</b>	150 x 16 mm
<b>Length x width x thickness</b>	150 x 16 x 8 mm
<b>Type description</b>	Corundum
<b>Gross Weight</b>	0.050 kg
<b>Product Group</b>	6HL