

Wet and dry safety vacuum cleaner ATTIX 791-2 M/B 1

Power consumption 1500 watt

**Nilfisk
ALTO**

Application:

Suction in continuous operation for dust classes L and M and ATEX Zone 22, all non-carcinogenic dust with MAK values > 0.1 mg/m³ and/or combustible dust from Zone 22.

Execution:

- Electronic follow-up control
- Secure suction into the filter; the whole system is completely de-dusted
- Variable speed control
- Tilting container for easy emptying
- With socket for power tools

Advantage:

- Brushless long-life motor

Delivery:

With 3.5-m suction hose AntiStatic (diameter 27 mm), tool adapter, filter element and filter bag, cable holder, rubberised 7.5-m mains cable



| | |
|---------------------------------|--------------------|
| Art. no. | 75524 011 |
| Brand | NILFISK-ALTO |
| Manufacturer Part Number | 30200 1537 |
| Model | ATTIX 791-2 M/B1 |
| Power input | 1500 W |
| Max. air delivery volume | 3800 l/min |
| Material of bins | Stainless steel |
| Underpressure | 250 mbar |
| Bin capacity | 70 l |
| Sound-pressure level | 59 dB |
| Weight | 25 kg |
| Cable length | 7.5 m |
| Length x width x height | 650 x 580 x 970 mm |
| Inner hose diameter | 27 mm |
| Hose length | 3.5 m |
| Nominal voltage | 230 V |
| Gross Weight | 32.000 kg |
| Product Group | 7AJ |

EAN

4005337063960