

## Pneumatic straight grinder G 352 H

MANNESMANN  
DEMAG

### Application:

For light and heavy deburring work

### Execution:

- Rear exhaust via hose unit with integrated silencer
- Safety lever valve conforms to EN 792
- Vane motor with powerful throughput

### Delivery:

Includes hose unit and collet chuck keys



<b>Art. no.</b>	<b>75061 070</b>
<b>Brand</b>	MANNESMANN DEMAG
<b>Manufacturer Part Number</b>	29946075
<b>Model</b>	G 352 H
<b>Valve design</b>	Lever valve
<b>Max. idle speed</b>	35000 rpm
<b>Min./max. idle speed</b>	0-35000 rpm
<b>Power output</b>	290 W
<b>Air consumption</b>	7.5 l/s
<b>Connection thread</b>	G 1/4 inch
<b>Sound-pressure level</b>	73 dB
<b>Length</b>	171 mm
<b>Diameter of housing</b>	30 mm
<b>Collet chuck diameter</b>	6 mm
<b>Suitable for max. sanding block diameter</b>	16 mm
<b>Max. HM rotating milling cutter diameter</b>	10 mm
<b>Weight</b>	0.36 kg
<b>Gross Weight</b>	1.309 kg
<b>Product Group</b>	7AA

### EAN

4251757300509