

CKJN clamp holder, negative, right

For copy, longitudinal and face turning with KNUX indexable insert

ATORN[®]

Application

For copy, longitudinal and face turning with KNUX indexable insert, 55°

Version

- Precision-manufactured steel support, burnished, hardened, adjustable clamp, type K, working angle 93°, tip angle 55°, clearance angle 0°

Advantage

- For copy, longitudinal and face turning particularly on low-performance machines
- Positive cutting geometry of the indexable insert ensures low cutting forces
- Broad range of use: suitable for both finishing and roughing operations



Art. No.	17825 010
ISO name	CKJN R/L 2020 K16
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Length of head	34 mm
Programming size	30 mm
Suitable for indexable inserts	KNUX 1604..
Tool design	Right
DIN	4983

EAN-Code

4050293127140