

## drilling hand vices

Mechanical clamping system

**ORION®**

### Application:

Secure clamping and fixing of workpieces on drills and measuring machines

### Execution:

- Basic body made of grey cast iron
- Universal means of attachment thanks to clamping slots and slotted holes
- Fixed clamping jaws with vee blocks
- Both jaws with step for clamping flat workpieces
- Black oxide-coated jaws and spindle

### Delivery:

1 pc. Handheld drill vice



<b>Art. no.</b>	<b>28660 200</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	28660200
<b>Jaws width</b>	100 mm
<b>Clamping width</b>	93 mm
<b>Jaws height</b>	30 mm
<b>Body length</b>	155 mm
<b>Body width</b>	155 mm
<b>Max. length</b>	185 mm
<b>Height</b>	63 mm
<b>Chip flute width</b>	15 mm
<b>Gross Weight</b>	5.100 kg
<b>Product Group</b>	282

### EAN

4039247171170