

LI-ION RECHARGEABLE LED FLEXIBLE INSPECTION LIGHT

Reference	MDM	EAN
887714	13276917	3660338410956

Description

Rechargeable LED Flexible Inspection Light.
 Magnet on the bottom with hook.
 Stepless dimming switch to adapt the brightness
 "Torch" mode if needed.



Applications



Technical characteristics

LED Type	Super bright 1x SMD + 1x COB LED
Lighting Power top light	120 lumens
Lighting Power main light	50/500 lumens
CRI	80 CRI+
CCT	6500K
Battery	3,7V 2600 mAh Li-ion Battery
Running time	Top light : 9,5h / Main light : 16h/2h
Charging time	4h

Standards and certifications

IP54 IK07

Packaging

- 1 unit, delivered with USB cable