

KERN EHA 1000-1



The compact all-round model with robust stainless steel weighing plate for use in laboratories, industries and for teaching



Measuring system

| | |
|---|-----------------------|
| Adjustment options: | External calibration |
| Linearity: | 300 mg |
| Number of weighing ranges: | 1 |
| Readability [d]: | 100 mg |
| Recommended adjusting weight: | 500 g (M1); 1 kg (M1) |
| Repeatability: | 300 mg |
| Resolution: | 10000 |
| Stabilisation time under laboratory conditions: | 3 s |
| Tare range: | 1 kg |
| Warm up time: | 30 min |
| Weighing capacity [Max]: | 1 kg |
| Weighing system: | Strain gauge |
| Weighing units: | g dwt ct oz gn |

Display

| | |
|-------------------------------|----------|
| Display digit height (large): | 2,200 cm |
|-------------------------------|----------|

Counting

| | |
|--|--------|
| Counting resolution: | 10000 |
| Minimum piece weight at piece counting (Laboratory): | 100 mg |
| Minimum piece weight at piece counting (Normal): | 1 g |

Functions

| | |
|--------------------|-----|
| Counting function: | yes |
|--------------------|-----|

Environmental conditions

| | |
|--------------------------------|-------|
| Maximum humidity: | 80 % |
| Maximum operating temperature: | 40 °C |
| Minimum ambient temperature: | 5 °C |

Power supply

| | |
|---------------------------------|---------------|
| Battery: | 2x1.5 V AA |
| Input voltage: | 100 V - 240 V |
| Mains adapter/adaptor included: | EURO CH UK |
| Operating time: | 70 h |

Services (optional)

Adjustment at the location of installation: 961-247

| | |
|--------------------|---------|
| DAkkS Certificate: | 963-127 |
|--------------------|---------|

Category

| | |
|----------------|----------------|
| Brand: | KERN |
| Category: | Balances |
| Product Group: | School balance |

Packaging & shipping


| | |
|-------------------------------|-------------------|
| Delivery: | 24 h |
| Dimensions packaging (WxDxH): | 245 x 204 x 76 mm |
| Gross weight: | 750 g |
| Net weight: | 500 g |
| Shipping method: | Parcel service |

Construction

| | |
|---------------------------------------|-------------------|
| Dimensions housing (WxDxH): | 225 x 160 x 50 mm |
| Dimensions of weighing plate (WxDxH): | 120 x 120 x 7 mm |
| Level indicator: | yes |
| Material weighing plate: | stainless steel |
| Revolving screw feet: | yes |
| Weighing surface (WxD): | 120 x 120 mm |

Piktogramme

STANDARD



OPTION

