

## SCLC steel boring bar set, offset, positive right

for face and longitudinal turning using CC indexable insert

**ATORN**<sup>®</sup>

### Application

For copy turning and longitudinal turning using CC indexable insert 80°.

### Version

- precision-manufactured **steel** boring bar, with inner cooling, offset, C type, 95° pitch angle, 80° tip angle, 7° clearance angle

### Advantage

- universal use for facing and longitudinal turning
- positive body geometry ensures low cutting forces

<b>Art. No.</b>	<b>17846 100</b>
<b>ISO name</b>	SCLC R06
<b>Material</b>	Steel
<b>Composition of set</b>	1 piece each 17846 168-174 (A0608H, A0810J, A1012K, A1216M)
<b>Number of pieces in assortment/set</b>	4 PCS
<b>Suitable for indexable inserts</b>	CC.. 0602..
<b>Machining direction</b>	Right
<b>DIN</b>	8024



### EAN-Code

4050293110159