

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: JENOLITE PAINT THINNER & BRUSH CLEANER

Product code: 89147 & 89148

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC9a: Coatings and paints, thinners, paint removers.

1.3. Details of the supplier of the safety data sheet

Company name: Jenolite UK Ltd
Chater Lea Buildings
Letchworth
Hertfordshire
SG6 1WT

Tel: 01462 480764

Email: Sales@Jenolite.net

1.4. Emergency telephone number

Emergency tel: 01462 480764
(office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Flam. Liq. 3: H226; Asp. Tox. 1: H304

2.2. Label elements

Label elements:

Hazard pictograms: GHS02: Flame
GHS08: Health hazard



Signal words: Danger

Precautionary statements: P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P241: Use explosion-proof equipment.
P280: Wear protective gloves/protective clothing/eye protection/face protection.
P301+P310: IF SWALLOWED: Immediately call a POISON CENTER or doctor.
P303+P361+P353: IF ON SKIN (or hair): Take off immediately all contaminated clothing.

SAFETY DATA SHEET

JENOLITE PAINT THINNER & BRUSH CLEANER

Page: 2

Rinse skin with water .

P331: Do NOT induce vomiting.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.1. Substances

Chemical identity: JENOLITE PAINT THINNER & BRUSH CLEANER

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Do not induce vomiting. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and pain.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Carbon dioxide. Alcohol or polymer foam. Dry chemical powder. Do not use water.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

[cont...]

SAFETY DATA SHEET
JENOLITE PAINT THINNER & BRUSH CLEANER

Page: 3

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method. Refer to section 13 of SDS for suitable method of disposal.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Ensure there is sufficient ventilation of the area. Smoking is forbidden.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area.

Suitable packaging: Must only be kept in original packaging.

Storage quantity limits: 250 L

7.3. Specific end use(s)

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits:

Respirable dust:

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	150 ppm	-	-	-

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Respiratory protection not required.

Hand protection: Protective gloves.

Eye protection: Tightly fitting safety goggles.

Skin protection: Protective clothing.

Environmental: Prevent from entering in public sewers or the immediate environment.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Colourless

Odour: Characteristic odour

[cont...]

SAFETY DATA SHEET

JENOLITE PAINT THINNER & BRUSH CLEANER

Page: 4

Evaporation rate: Slow

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Not miscible

Boiling point/range°C: 150 - 200

upper: 6

Vapour pressure: 300 Pa @ 20 deg C

Flammability limits %: lower: 0.6

Flash point°C: 40

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

10.4. Conditions to avoid

Conditions to avoid: Direct sunlight. Sources of ignition.

10.5. Incompatible materials

Materials to avoid: Strong acids. Strong bases. Strong oxidising agents.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Toxicity values:

Route	Species	Test	Value	Units
DERMAL	RBT	LD50	>5000	mg/kg
ORAL	RAT	LD50	>5000	mg/kg
VAPOURS	RAT	4H LC50	>5000	mg/l

Relevant hazards for product:

Hazard	Route	Basis
Aspiration hazard	-	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

[cont...]

SAFETY DATA SHEET

JENOLITE PAINT THINNER & BRUSH CLEANER

Page: 5

Eye contact: There may be irritation and pain.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Other information: Not applicable.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

12.3. Bioaccumulative potential

12.4. Mobility in soil

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Recovery operations: Solvent reclamation/regeneration.

Waste code number: 08 01 11

Disposal of packaging: Retain for recovery.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1263

14.2. UN proper shipping name

Shipping name: PAINT RELATED MATERIAL

14.3. Transport hazard class(es)

Transport class: 3

14.4. Packing group

Packing group: III

[cont...]

SAFETY DATA SHEET
JENOLITE PAINT THINNER & BRUSH CLEANER

Page: 6

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: D/E

Transport category: 3

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.