

T-slot bolts



Application:

For clamping workpieces on machine tables.

Execution:

- Tempered
- Rolled thread
- Forged
- With milled groove guide
- M8 to M12, strength class 10.9
- M16 to M24, strength class 8.8
- DIN 787



Art. no.	26200 245
Brand	AMF
Manufacturer Part Number	330126
DIN	787
Thread dimension	M10
Groove width	10 mm
Length excluding head	160 mm
Outer diameter	9.7 mm
Length of head	15 mm
Head height	6 mm
Gross Weight	0.119 kg
Product Group	260