5500 Lit Rocker Switches - Single Pole 16A 250Vac





16(4)A 250Vac T85 10(3)A 250Vac T100, (12A 250Vac T125 for P rocker only)




UL CSA 15A 250Vac, CSA 16A Non Ind 250Vac UL CSA 250Vac 1hp, 125Vac 1/2hp UL 85°C, file E45221, CSA file LR10990




(In house test) Inrush 24A to EN61058-1 & 20A 28Vdc

Technical data on pages 4 & 5 (switches), 66 (indicators)

For Twin units repeat the order details for both the right and left sides











C5500AL ---

C5503PL ---







C5503A/C5503AL



C5503P/C5503PL

BODY Panel cut-out ** Flange Cut-outs must be punched in the direction of insertion Α 30.2 Matt only В R3 5 30.0 30.1 11.0/11.1 Matt only R1.0 30.0 30.1 31.9 11.0/11.1 Matt only Q R1.6 28.2 28.3 **►**14.0**►** 11.5/11.6 Gloss or Matt R 28.5 28.6 14.0/14.1 Matt only

T

11.5/11.6

Matt only

OPTIONS

Finish Matt is standard

Colour Call factory for custom colours. A full range is available for large orders

Legend printing Select from the examples or call factory for custom legends

Lamp voltage Call factory for details

Blanking plate A0434 -- (SP) A0494 -- (DP) Dummy units to fill unused panel holes


Protective cover (designed to IP65) Snaps on to A, L, Q or T bodies (add G after body in cat no). This reduces panel thickness by 1mm.



Panel sealing washers W46 (Single Pole) and W42 (Double Pole) are available for these body types but reduce panel thickness by a further 0.8mm

For all options call the factory

DIMENSIONS (mm)




Panel thickness A,Q 0.75 to 3.3mm L,B,T 0.75 to 2.5mm 0.75 to 3.0mm R ** For cut-out details on momentary switches

call the factory

Terminal spacing - Poles 10.8 between centres (twin units)

Twin units

Two single switches or a switch and an indicator light can be assembled side by side in one double pole body. For 1500 range panel cut-out details see page 29. For 5500 range panel cut-out details (L, B and T) call factory.







For twin units the first set of order format details refer to the left hand unit, when looking at the front of the assembly (This has terminal numbers 1, 2 & 3)

Examples of printing







23

Technical Information - Switches and Fuseholders

Most major technical information is shown on each specific product page, other details are grouped here for easy reference. Details shown here apply to most switches and fuseholders.

Snap-action switches (pages 42, 45 and 48-51), indicators (pages 66-78) and connectors (pages 79-81) have product specific information within the section.

MATERIALS Body and actuator (opaque)	MOST PRODUCTS .Nylon 6.6	EXCEPTIONS . 8300V, 1900V, 0916V & 0911V bezels & actuators are stainless steel 0600 and 3900 actuators are plated brass
Actuator (transparent)	Polycarbonate	
Current carrying parts	.Copper Alloy	
Contact points	.Silver Alloy	. N/A for 0055/56, 0600/2, 0916-0920, 0017,
		2000 & 3005/3006. Gold plated for 1100.

PROPERTIES

Electrical

PROPERTIES

Physical

Humidity resistance at 91-95% relative humidity

(to subsequently comply with requirements of the

Dielectric strength test)

Impact resistance

>0.5Nm

Storage temp. (1 year period)

<125°C

Some discolouration of terminals may occur

Flame retardancy

UL94V2

Solderability to BS 2011 pt.2.1T - (with an iron)

6 secs at 350°C

Angular movement ± 4° overall (where applicable)

38°

1250, 6000, 8500, 8550, 8600, 8650, 8800 - 26°

Force to operate

2.0N - 20.0N

Call factory for specific values

Fixing nut torque (where applicable)

1.0Nm (8.91 lb/in) nom.

Call factory for specific values

GENERAL INFORMATION

ALL SWITCHES

Heat and Fire resistance Category D.
Ingress Protection without cover is IP40.
Higher ratings where available will be shown on the relevant catalogue page.

ALL PRODUCTS

Solder terminals should not be fitted with "Push on", "QD" or "Fast on" type cable connectors.

Panel holes must be punched in the direction of insertion.

Items marked lack on on the following pages are assembled automatically. This ensures the highest attainable quality at a competitive price.

All products should be applied, installed and maintained by the customer using competent persons in accordance with good electrical practice. Products should be tested by the customer in the application to ensure suitability. Special care should be taken not to expose switches to water, dust, corrosive chemicals, silicone, excessive solder flux, cyanoacrylate adhesives, severe impact, extremes of temperature, electrical supply voltage or load current in excess of the specified limits.

Transparent lenses on indicator lights and lit switches are moulded in polycarbonate, a material which is attacked by organic chemicals and animal or vegetable fats.

Please contact the factory for advice on these products.

For performance in accord with the stated ratings, switch actuators should be fully depressed and fully released during operation.

WEIGHTS OF OUR MOST FREQUENTLY SUPPLIED PRODUCTS, not including packaging.

Product gms	Product gms	Product gms	Product gms	Product gms
0055, 0056 5.7/6.8	1048 2.8	1570 12.7	5500 7.1	8353 5.9
0305 32.9	1091FH 12.6	1584-1589 11.1	5503 7.8	8500
0333 4.5	1091FL 52.8	1700H 8.4	5567 14.3	8550 4.8
0345 8.9	1100 2.0	1750H 13.2	6050 13.58	8553 5.2
0340 sw only 7.12	1250SP 5.9	17500 25.6	6053 14.15	8600 3.5
0340K/P 25.0	1250DP 7.0	2000 2pos C SP 3.8	7000 10.4	8620 4.3
0430 5.5	1300 5.7	2000 2pos C DP 4.5	7050 12.3	8650 6.3
0589 3.5	1350 11.2	2000 5pos A SP 6.3	7053 12.9	8670 8.5
0711-1S 16.6	1500 5.7	2000 5pos A DP 7.3	8250 4.9	8800 2.9
0712-S 27.8	1520 6.6	T2225B 5.0	8300 4.0	9100 20.0
0717-1S 22.4	1550 11.2	2950 5.3	8350 5.0	
0900S/L 2.6/2.9	1553 11.8	3111 11.8	8350RP 34.0	

Technical Information - Indicators

The majority of Arcolectric indicator lights can be supplied with alternative light sources:

Neon, Fluorescent, Filament lamp or LED.

NEON and FLUORESCENT LAMPS

Colours

Red, Amber and Clear neon, Green fluorescent.

Maximum striking voltages

Standard brightness types 65Vac 90Vdc, High brightness types 85Vac 135Vdc. High brightness types are usually fitted.

Life

Typically 25,000 hours (Green fluorescent lamps 20,000 hours). (Measured to a point when the light output of the lamp is half its original level.)

The end of life for a neon lamp is not usually a sudden failure.

False signals due to long wiring

It is possible for neon or fluorescent tubes to glow when they should be off. The false signal is caused by the capacitance effect of fairly long wiring to the indicator being adjacent to other live cables.

This effect can be prevented in most cases by fitting a 100K resistor across the supply wires close to the indicator assembly.

MATERIALS

Moulded bodies and bases Nylon 6.6

Metal bodies and bezels Chrome plated brass (except #)

Lenses Polycarbonate

Terminals (most types)

Brass (electro-tin plated)

Terminals (exceptions)

Brass (flash silver* or nickel** plated)

Threaded metal nuts

Brass (nickel plated on 0275/7)

Other fixings Call factory for details

* R9, 0061, 0062, 0430, 0480, 1090, 1091, 6030, 7030, 8630, 8580 ** # 3130, 3160, 3161, 3221 have nickel plated terminals with steel screws and plated polyamide bezel trims

TEMPERATURE RATING

Authority	with Terminals	with Wire leads	
		PVC	SILICONE
European	T125°C	T105°C	T125°C
UL	T65/75°C	T65/75°C	

SYMBOLS













FILAMENT LAMPS

Colours

Red, Amber, Green, (Clear and Blue - check availability)

LEDS

Colours

Red, Yellow and Green.

Voltage

Basic voltage 2.0/2.2V. Some items are available with integral resistors for 12V use. For details of resistors required for higher voltages, please call the factory.

Current

Maximum continuous forward current 35mA.

Life

>100.000hrs

Polarity

LED flat side is - negative, round side + positive.