

Angular milling cutter 90°

For indexable milling inserts LN.X 1510..

ATORN®

Application


4 flutes per indexable milling insert and special chip shape geometry for profitability and high cutting rates when milling faces, milling corners, trimming and milling grooves.

Version

- Wear-resistant, nickel-plated version
- With internal cooling

Advantage

- 4 cutting edges on one double-sided indexable insert
- Special chip shape geometry for low power consumption
- Thick inserts



Art. No.	16016 500
Cutting edge diameter	100 mm
Length	50 mm
Bore diameter	32 mm
max. ap	14 mm
Number of cutting edges	8 PCS
Suitable indexable insert no.	2

EAN-Code

4050293344417